

Search Results

Evaluate

- Advertisements
- PDF-QuickNet Cab
- FAQs
- Technical References
- PDF-QuickNet MTP ..
- PDF-Maintaining ..
- PDF-QuickNet MTP ..
- White Papers
- PDF-Best Practic ..

Design a Solution

- Best Practices
- PDF-Visual Insp ..
- Part Drawings
- PDF-Fiber Optic ..
- Specification Sheets
- PDF-QuickNet MTP ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Visual Insp ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 **Text Search: 'FX12D5-5M4Y'**

Your search criteria matched only one product, shown below

**FX12D5-5M4Y**



- Pass all TIA/EIA-568-B.3 performance requirements
- FOCIS-5 compliant
- Insertion loss per mated pair: 0.50dB typical; 0.75dB max.
- Tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters at 850nm with 50/125µm (OM3) laser optimized fiber
- Backward compatible with all 50/125µm (OM2) MPO or MTP\* system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss and return loss data recorded for every 10Gig™ Multimode Interconnect Cable Assembly
- Lifetime traceability of test data to a Q.C. number on each cable assembly

\* MTP is a registered trademark of US Conec Ltd.

Additional lengths and availability: Interconnect cable assemblies are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. To order lengths other than 1 meter, replace the 1 after the M (FX12D5-5M1(Y)) with the desired length (FX12D5-5M2(Y) for 2 meter length). For other lengths or male MTPs\*, contact Customer Service for actual lead times.

▪ Part Number	FX12D5-5M4Y
▪ RoHS Compliance Status	Compliant
▪ Part Description	Female MTP* to female MTP* 12-fiber interconnect cable assembly (one female MTP* connector on each end on ribbon interconnect cable) – 10Gig™ 50/125µm. Outside diameter: 5mm x 2.5mm.
▪ Product Type	MTP* 12 Fiber Interconnect Cable Assemblies
▪ Material	PVC
▪ Color	Aqua
▪ Length (m)	4
▪ Fiber Compatibility	10 GbE 50/125µm
▪ Fiber Cable Size	5mm x 2.5mm
▪ Fiber Type	Multimode
▪ Cable Type	OM3 50 Micron
▪ CE Compliant	No
▪ Connector 1 Type	MTP* Connector
▪ Connector 2 Type	MTP* Connector
▪ End Configurations	MTP* to MTP*
▪ Fiber Count	12
▪ Flammability Rating	Plenum (OFNP)
▪ No. of Fibers	12
▪ Pricing Description	MTP*-MTP* Interconnect Cable Assembly 4m 10 GbE 50µm
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.