



UNIT: mm



PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 5Mohm(min)
4. dielectric test: DC 300V

1PCS/PE BAG

⑨	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+ "10PCS"	CNC Tech, LLC Industrial Cable and Connector Technology DRAWN Andy CHECKED APPROVAL DECIDED VERSIONS/EDITION A/0 PROJECTION 102-1010-BE-00300 2013-8-23 2013-8-23
⑧	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"	
⑦	TIE	1	WHITE L=100mm	
⑥	IN JACKET	3g	CLEAR LDPE (MOULD NO: NM-027)	
⑤	OUT JACKET	7g	BEIGE (IV-29#) PVC-40P (MOULD NO: NM-83)	
④	OUT JACKET	6g	BEIGE (IV-29#) PVC-40P (MOULD NO: NM-40)	
③	CABLE	1	BEIGE (IV-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=3000 ± 10mm	
②	CONN	1	USB2.0 A FEMALE SHELL: NICKEL PIN G/F SHORT TYPE INSULATOR COLOR: WHITE	
①	CONN	1set	USB2.0 A MALE SHELL: NICKEL PIN G/F 4PCS-TYPE INSULATOR COLOR: WHITE	
NO.	NAME	Q' TY	SPECIFICATION	

—

B

→

C

—

D

A

—

B

←

C

—

D

A