

VS-BU-CD-HD-1,0/13,5/0,37

Order No.: 1655263

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1655263>

Crimp contact, for D-SUB contact inserts with high density, socket,
connection cross section AWG 22, turned, gold-plated

Commercial data

GTIN (EAN)	4046356029209
sales group	D502
Pack	100 pcs.
Customs tariff	85369010
Weight/Piece	0.00013 KG
Catalog page information	Page 324 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
09/06/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data**General data**

Ambient temperature (operation)	-55 °C ... 125 °C
Insertion/withdrawal cycles	≥ 200
Conductor cross section	0.34 mm ²
Connection cross section AWG	22

Material data

Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel

Electrical characteristics


Rated voltage (III/3)	60 V
Rated surge voltage	1 kV
Rated current	3 A
Insulation resistance	≥ 5 GΩ

Accessories

Item	Designation	Description
General		
1658503	VS-IET-DSUB-SIGNAL-HD	Insertion/extraction tool, to insert and extract the D-SUB high density signal contacts

Diagrams/Drawings

Dimensioned drawing



D-SUB crimp contact socket

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;