




KLEPS 2 BU schwarz/black

Industrial Connectors: Measuring and Testing Equipment: Clamp-type test probes: 2 mm system

Product description

Description	Miniature clamp-type test probe with 2 mm diameter socket connection. Gold-plated copper beryllium contact spring. Gold-plated sprung bronze contact hook for wires up to a maximum diameter of 2 mm. Suitable for connection to wrap posts up to a maximum of 1x1 mm.
Type	KLEPS 2 BU schwarz/black
Order No.	973 501-100
System	2 mm system
Clamping range	2 mm
Clamp type	contact hook
Housing Color	black
Other standard types	red color, order no. 973 501-101

Drawing



Technical data

Type of contact	socket (spring-loaded)
Type of termination	plug
Rated voltage	DC 60 V
Rated current	6 A
Contact resistance	15 mOhm

Material

Contact material	contact hook: bronze, contact spring: copper beryllium
Contact surface material	gold-plated
Housing material	PBT

Environmental conditions

Temperature range	-25 °C to +100 °C
-------------------	-------------------

Inflammability class

