

D35 Euro Wall Mount 1-3 Watts Series

Features

- 230 VAC Input
- Euro Wall Plug Style
- Rated for Continuous Duty
- Filtered
- Unregulated Outputs up to 3 Watts
- Meets Safety Agency Requirements
- CE Compliant
- Impact Resistant Polycarbonate Enclosure
- Private Label Marking Available
- 1 Year Warranty
- Modified and Custom Designs Also Available
- Manufactured in China

Ault Model	Rated Output Volts DC	Maximum Current-Amps	Maximum Watts
D35-050400-A000G	5	0.40	2.0
D35-060333-A000G	6	0.33	2.0
D35-060400-A000G	6	0.40	2.4
D35-070400-A000G	7	0.40	2.8
D35-080375-A000G	8	0.37	3.0
D35-090140-A000G	9	0.14	1.3
D35-090333-A000G	9	0.33	3.0
D35-100300-A000G	10	0.30	3.0
D35-110273-A000G	11	0.30	3.0
D35-120250-A000G	12	0.25	3.0
D35-140214-A000G	14	0.21	3.0
D35-150200-A000G	15	0.20	3.0
D35-180167-A000G	18	0.17	3.0
D35-200150-A000G	20	0.15	3.0
D35-210143-A000G	21	0.14	3.0
D35-220136-A000G	22	0.14	3.0
D35-240125-A000G	24	0.13	3.0

Input

- Voltage 230 VAC
- Line Frequency 50 Hz
- Connector Euro Wall Plug, No Ground

Electrical

- Topology DC Unregulated Power Supply
- Dielectric Withstand 3000 VAC primary-secondary
1500 VAC primary-core
500 VAC secondary-core
- Protection Current, Thermal or Energy Limiting
- EMI Complies with EMC Directives
- CE CE Compliant

Safety Approvals

- Safety Agencies EN60950 or EN60742

Environmental

- Operating Temperature 5° to 40° C with no derating
- Storage Temperature -30° to +85° C
- Relative Humidity 5% to 95% non-condensing
- Altitude 0-10,000 feet
- Cooling Convectional - non vented case

Mechanical

- Case Dimensions D35 - Euro Wall Plug
2.4 L x 1.8 W x 1.4H (in)
61 L x 45 W x 34 H (mm)
- Case Material Black 94 V1 Polycarbonate
- Weight 8 ounces, 220 grams,
(excluding cord)
- Cord and Connector 6 ft., 2 Conductor, 22-24 AWG
Ault #3 Connector
Other Connectors Available

ONE YEAR WARRANTY

