



PM-010/PM-132

PCMCIA 2xRS232 1MBaud

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Features

- 2 port RS232
- PCMCIA socket size
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



PM-010:
PCMCIA 2xRS232
1MBaud

PM-132
PCMCIA 2xRS232
RUGGED 1MBaud



This product works in Windows CE up to 115,200 baud (full duplex mode only)

Description

A PCMCIA type II card providing two independent RS232 serialports. Velocity megabaud data transfer rates and the 128 byte deep FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your laptop. Being mobile no longer limits your options.

Being mobile no longer limits your options. Standard and ruggedised card options to suit your needs.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows Vista 32 bit and 64 bit editions
- Windows XP 32 bit & 64 bit editions
- Windows 2000
-



As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



ORDER

Description

PCMCIA 2xRS232 1MBaud

PCMCIA 2xRS232 RUGGED 1MBaud

Code

PM-010

PM-132



PCMCIA 2xRS232 1MBaud

PM-010/PM-132: Full Specification

Port 	Ports Connector FIFO size Operating Distance Cable	2 x RS232 DB9 connector (9 Pin Male) 128 RX FIFO + 128 TX FIFO EIA - RS232 Standard 2 Port Cable: DB9 connector (9 Pin Male)
Port Settings 	Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes	921,600 5,6,7 or 8 Odd, Even, None, Mark or Space 1, 1.5 or 2 RTS/CTS , DTR/DSR Point to Point
Interface 	OS Compatibility BUS	Microsoft Windows CE Windows Server 2003 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions Microsoft Windows 2000 Microsoft Windows 95 PCMCIA
Approvals 	Other Approvals Microsoft Approvals	RoHS PCMCIA Affiliate Member EMC: CE FCC Compliant Microsoft Certified Gold Partner Microsoft Windows 95 Windows Vista 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions Microsoft Windows 98
General	PCB Layers Power Consumption Weight Size	4 210mA @ 5V, 20mA @ 12V 0.027 Kg PCMCIA Type II: 85.6 x 54 x 5.0 mm
Box Content	Packaging Card	Installation CD including manual, Microsoft signed drivers & utilities PCMCIA 2xRS232 1MBaud / PCMCIA 2xRS232 RUGGED 1MBaud (2 Port Cable: DB9 connector (9 Pin Male))
Product Support 	Warranty Support	Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional 	OEM option Made In Customisable	Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com

This product works in Windows CE up to 115,200 baud (full duplex mode only)

Datasheet Version: 3.6 Published on: 2009/7/20