

Product Sheet. Part numbers: ASM20I, ASM25I, ASM32I

- AS..I IP68 degree of protection (EN 60529)
- temperature range -25 °C / +100 °C
- metric threading according to EN 60423 and EN 50262
- anti-aging rubber gaskets
- **ASM20I RAL 7035. ASM25I & ASM32I RAL 7001**
- UL, VDE, CSA approval


**complete insulating
cable gland**



description	part No.		
	M threading		
- for cable Ø 5 - 12.5 mm	AS M20I	grey	M 20
- for cable Ø 5 - 12.5 mm	AS M20IN	black	M 20
- for cable Ø 9 - 18 mm	AS M25I		M 25
- for cable Ø 14 - 25 mm	AS M32I		M 32
- for cable Ø 18 - 32 mm*	AS M40I		M 40
- for cable Ø 24 - 38.5 mm*	AS M50I		M 50

dimensions in mm

AS C..I - AS M..I



AS M..I	A	CH
20	10	24
25	10	33
32	10	42
40	10	53
50	12	60

Dimensions indicated are not binding and may be changed without prior notice.