





rev	ecn no	dr	date
A	S06-0192	KHL	2006-06-01
B	S06-0233	KHL	2006-07-10
C	S06-0385	KHL	2006-11-21
D	S07-0081	KHL	2007-03-01
E	S10-0205	PR	2009-12-02
-	-	-	-
-	-	-	-

www.fciconnect.com				surface - ✓ ISO 1302	tolerance std ISO 406 ISO 1101	projection ⊕	MM
				TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	KH LEE	2006-06-01	ANGULAR	LINEAR	0.X	±-	size A3
Eng	KH LEE	2006-06-01			0.XX	±0.25	
Chr	KH LEE	2009-12-02	0° ±3°		0.XXX	±-	ECN S10-0205
Appr	JOEY NG	2009-12-02	Product family			MINITEK	Spec ref -
MINITEK II R/R SMT STR DUPEX HDR				dwg no			10069527
				Rev.			E
catalog no				CUSTOMER			sheet 1 of 2



Copyright FCI.

A

B

C

D

PRODUCT NO.	POS	DIM X	DIM Y	DIM A	DIM B	DIM W	POL. POS	CONTACT PLATING	MAT'L COLOR	TUBE PACK'G AVAILABLE	TUBE W CAP PACK'G AVAILABLE
10069527-001LF	2X5	8	10	5.5	2.4	2.25	-	0.76µm MIN Au	BLACK	-	-
10069527-002LF	2X4	6	8	4.0	7.5	2.25	-	0.76µm MIN Au	BLACK	-	-
10069527-003LF	2X4	6	8	4.5	3.0	2.25	-	0.76µm MIN Au	BLACK	-	-

NOTES:

- MATERIAL:
BODY : GLASS FILLED PCT UL 94V-0 (REFER TO TABLE FOR COLOR)
PIN : PHOSPHOR BRONZE
- TOLERANCE UNLESS OTHERWISE NOTED ± 0.25
- DIM 1.0 ± 0.15 FOR MOLDED SIDE(S) ONLY. IF SIDE(S) ARE BROKEN, DIM 1.5 MAX APPLIES
- RECESS APPLIES TO MOLDED SIDE(S) ONLY.
- POLARISATION BY OMISSION OF PIN. POSITION REFER TO TABLE
- STANDARD PACKAGING IN PLASTIC BAG.
- P/N 10069527-XXXTC TO BE PACKED IN TUBE WITH PICK-UP CAP INSTALLED IN THE CENTRE OF PRODUCT. SEE FIG. 1. REFER TO TABLE FOR AVAILABILITY.
- P/N 10069527-XXXT TO BE PACKED IN TUBE. REFER TO TABLE FOR AVAILABILITY.
- P/N 10069527-XXXTR TO BE PACKED WITH TAPE AND REEL (OPTIONAL: PICK-UP CAP). FCI MUST BE CONTACTED FOR AVAILABILITY IN SIZE REQUESTED.
- SOLDER TAIL PLATING:
2.54µm MIN 100% MATTE TIN PLATING OVER 1.27µm MIN NICKEL UNDERPLATE.
- PRODUCT DESCRIPTION CODE:
XXXXXXXX - XXXLF
LEAD FREE SEE NOTE 12 & 13
EXTENSION NUMBER
BASE NUMBER
- THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN..
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

PICK-UP CAP






FIG. 1



RECOMMENDED PAD LAYOUT

CONFIDENTIAL

www.fciconnect.com			surface - 		tolerance std ISO 406 ISO 1101		projection 		 MM		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	KH LEE	2006-06-01	ANGULAR 0° ±3°		LINEAR		0.X	±-	size A3	Scale 8:1	
Eng	KH LEE	2006-06-01					0.XX	±0.25			
Chr	KH LEE	2009-12-02					0.XXX	±-			
Appr	JOEY NG	2009-12-02	Product family				MINITEK		Spec ref -		
		title MINITEK 11 R/R SMT STR DUPEX HDR				dwg no 10069527				Rev. E	
		catalog no -				CUSTOMER		sheet 2 of 2			