




art. no.	R_{th} [K/W]	⚡
ICK 35 SA	15	TO 220




SK 12 SA 32




SK 12 SA 2 x 32




art. no.	R_{th} [K/W]	⚡
SK 12 SA 32	30	1 x SOT 32
SK 12 SA 2 x 32	15	2 x SOT 32




SK 13 35 SA 220




SK 13 35 SA 220 3,2




SK 13 35 SA 220 3,5




art. no.	R_{th} [K/W]	⚡
SK 13 35 SA 220	17	TO 220
SK 13 35 SA 220 3,2	17	TO 220
SK 13 35 SA 220 3,5	17	TO 220




SK 431 1



SK 431 2



SK 431 3



art. no.	R_{th} [K/W]	⚡
SK 431 1	18	TO 220
SK 431 2	18	TO 220
SK 431 3	18	TO 220

surface: black anodised