

STRAIGHT MALE CORD CONNECTORS

E1

IP66*
SUITABILITY



UL Listed to Type 4, 4X, 12
and Type 13

WIRE MANAGEMENT

Straight Male

N.P.T. Hub Size	Cord Dia. Inches (mm)	Form Size	Colour Code	Machined Aluminum	Machined Zinc-Plated Steel	Stainless Steel	Nylon Gray	Nylon Black
 Machined Aluminum	.06"–.13" (1.6–3.2)	F1	Green	—	—	—	SHC1001CR	—
	.13"–.19" (3.2–4.7)		Orange	SHC1002	—	—	SHC1002CR	—
	.19"–.25" (4.7–6.3)		Red	SHC1003	—	SHC1003SS	SHC1003CR	—
	.25"–.31" (6.3–7.9)		Black	SHC1004	—	SHC1004SS	SHC1004CR	—
	.31"–.38" (7.9–9.5)		White	SHC1005**	—	—	SHC1005CR	SHC2005CR
	.38"–.44" (9.5–11)		Blue	—	—	—	SHC1006CR	—
	.06"–.13" (1.6–3.2)		Green	SHC1007	—	—	—	—
	.13"–.19" (3.2–4.7)		Orange	SHC1008	SHC1008ZP	—	SHC1008CR	SHC2008CR
 Machined Zinc-Plated Steel	.19"–.25" (4.7–6.3)	F1	Red	SHC1009	—	SHC1009SS	SHC1009CR	—
	.25"–.31" (6.3–7.9)		Black	SHC1010	SHC1010ZP	—	SHC1010CR	SHC2010CR
	.31"–.38" (7.9–9.5)		White	SHC1011	—	SHC1011SS	SHC1011CR	SHC2011CR
	.38"–.44" (9.5–11.0)		Blue	SHC1012	SHC1012ZP	SHC1012SS	SHC1012CR	SHC2012CR
	.19"–.25" (4.7–6.3)		Red	SHC1015	—	—	—	—
	.25"–.31" (6.3–7.9)		Black	SHC1016	—	—	—	—
	.31"–.38" (7.9–9.5)		White	SHC1017	—	—	—	—
	.38"–.44" (9.5–11.0)		Blue	SHC1018	—	—	—	—
1/2	.06"–.13" (1.6–3.2)	F2	Green	SHC1019	—	—	SHC1019CR	—
	.13"–.19" (3.2–4.7)		Orange	SHC1020	SHC1020ZP	SHC1020SS	SHC1020CR	—
	.19"–.25" (4.7–6.3)		Red	SHC1021	SHC1021ZP	SHC1021SS	SHC1021CR	SHC2021CR
	.25"–.38" (6.3–9.7)		White	SHC1022	SHC1022ZP	SHC1022SS	SHC1022CR	SHC2022CR
	.38"–.50" (9.7–12.7)		Blue	SHC1023	SHC1023ZP	SHC1023SS	SHC1023CR	SHC2023CR
	.50"–.63" (12.7–15.9)		Brown	SHC1024	SHC1024ZP	SHC1024SS	SHC1024CR**	SHC2024CR**
	.38"–.50" (9.7–12.7)		Blue	SHC1025	—	—	—	—
	.50"–.63" (12.7–15.9)		Brown	SHC1026	—	—	—	—
1/2	.63"–.75" (15.9–19.0)	F3	Yellow	SHC1027**	SHC1027ZP**	—	—	—
	.75"–.88" (19.0–22.2)		Orchid	SHC1028**	SHC1028ZP**	—	—	—

Note: * IP66 Suitability when used with optional metal clad O-ring.

** Cable jacket may have to be stripped to pass through connector body.



STRAIGHT MALE CORD CONNECTORS

IP66*
SUITABILITY



UL Listed to Type 4,
4X, 12 and Type 13

Straight Male

N.P.T. Hub Size	Cord Dia. Inches (mm)	Form Size	Colour Code	Machined Aluminum	Machined Zinc-Plated Steel	Stainless Steel	Nylon Gray	Nylon Black
3/4	.06"-.13" (1.6-3.2)	F2	Green	SHC1029	—	—	—	—
	.13"-.19" (3.2-4.7)		Orange	SHC1030	SHC1030ZP	—	—	—
	.19"-.25" (4.7-6.3)		Red	SHC1031	SHC1031ZP	—	—	—
	.25"-.38" (6.3-9.7)		White	SHC1032	SHC1032ZP	—	—	—
	.38"-.50" (9.7-12.7)		Blue	SHC1033	SHC1033ZP	—	—	—
	.50"-.63" (12.7-15.9)		Brown	SHC1034	SHC1034ZP	—	—	—
	.38"-.50" (9.5-12.7)		Blue	—	SHC1035ZP	SHC1035SS	SHC1035CR	SHC2035CR
	.50"-.63" (12.7-15.9)		Brown	SHC1036	—	SHC1036SS	SHC1036CR	SHC2036CR
3/4	.63"-.75" (15.9-19.0)	F3	Yellow	SHC1037	SHC1037ZP	SHC1037SS	SHC1037CR	SHC2037CR
	.75"-.88" (19.0-22.2)		Orchid	SHC1038**	SHC1038ZP**	SHC1038SS**	SHC1038CR**	SHC2038CR**
	.50"-.63" (12.7-15.9)		Brown	—	SHC1097ZP	—	—	—
	.63"-.75" (15.9-19.0)		Yellow	—	SHC1098ZP	—	—	—
1	.75"-.88" (19.0-22.2)	F3	Orchid	—	SHC1099ZP	—	—	—
	.38"-.50" (9.7-12.7)		Blue	SHC1039	—	—	SHC1039CR	—
	.50"-.63" (12.7-15.9)		Brown	SHC1040	—	—	SHC1040CR	SHC2040CR
	.63"-.75" (15.9-19.0)		Yellow	SHC1041	—	SHC1041SS	SHC1041CR	SHC2041CR
	.75"-.88" (19.0-22.2)		Orchid	SHC1042	—	SHC1042SS	SHC1042CR	SHC2042CR
	.88"-1.00" (22.2-25.4)		Gray	SHC1043	SHC1043ZP	—	SHC1043CR	SHC2043CR
	1.00"-1.13" (25.4-28.6)		Pink	SHC1044**	—	SHC1044SS**	SHC1044CR**	SHC2044CR**



Stainless
Steel



Gray Nylon



Black Nylon

Note: * IP66 Suitability when used with optional metal clad O-ring.

** Cable jacket may have to be stripped to pass through connector body.

Form 4 aluminum and plated steel nuts are machined, bodies are cast aluminum.

STRAIGHT MALE CORD CONNECTORS

E3

IP66*
SUITABILITY



UL Listed to Type 4,
4X, 12 and Type 13

WIRE MANAGEMENT

Straight Male

N.P.T. Hub Size	Cord Diameter Inches	(mm)	Form Size	Cast Aluminum	Malleable Iron
1	.88"-1.00"	(22.2-25.4)	F5	SHC1046	—
	1.00"-1.13"	(25.4-28.6)		SHC1047**	—
	1.13"-1.25"	(28.6-31.7)		SHC1048**	—
	1.25"-1.38"	(31.7-34.9)		SHC1049**	—
	.75"- .88"	(19.0-22.2)		SHC1050	—
1-1/4	.88"-1.00"	(22.2-25.4)	F5	SHC1051	—
	1.00"-1.13"	(25.4-28.6)		SHC1052	SHC1052ZP
	1.13"-1.25"	(28.6-31.7)		SHC1053	SHC1053ZP
	1.25"-1.38"	(31.7-34.9)		SHC1054**	SHC1054ZP
1-1/2	.75"- .88"	(19.0-22.2)	F5	SHC1055	—
	.88"-1.00"	(22.2-25.4)		SHC1056	—
	1.00"-1.13"	(25.4-28.6)		SHC1057	SHC1057ZP
	1.13"-1.25"	(28.6-31.7)		SHC1058	SHC1058ZP
	1.25"-1.38"	(31.7-34.9)		SHC1059	SHC1059ZP
1-1/2	1.38"-1.50"	(34.9-38.1)	F6	SHC1061	—
	1.50"-1.63"	(38.1-41.3)		SHC1062**	—
	1.63"-1.75"	(41.3-44.4)		SHC1063**	—
	1.75"-1.88"	(44.4-47.6)		SHC1064**	—
	1.25"-1.38"	(31.7-34.9)		SHC1065	—
2	1.38"-1.50"	(34.9-38.1)	F6	SHC1066	—
	1.50"-1.63"	(38.1-41.3)		SHC1067	—
	1.63"-1.75"	(41.3-44.4)		SHC1068	—
	1.75"-1.88"	(44.4-47.6)		SHC1069	—
2	1.69"-1.81"	(42.9-46.0)	F7	SHC1070	—
	1.81"-1.94"	(46.0-49.2)		SHC1071	—
	1.94"-2.06"	(49.2-52.4)		SHC1072**	—
	2.06"-2.19"	(52.4-55.6)		SHC1073**	—
	2.19"-2.31"	(55.6-58.7)		SHC1074**	—
2-1/2	1.69"-1.81"	(42.9-46.0)	F7	SHC1076	—
	1.81"-1.94"	(46.0-49.2)		SHC1077	—
	1.94"-2.06"	(49.2-52.4)		SHC1078	—
	2.06"-2.19"	(52.4-55.6)		SHC1079	—
	2.19"-2.31"	(55.6-58.7)		SHC1080	—
	2.31"-2.44"	(58.7-61.9)		SHC1081**	—
3	1.69"-1.81"	(42.9-46.0)	F7	SHC1086	—
	1.94"-2.06"	(49.2-52.4)		SHC1088	—
	2.06"-2.19"	(52.4-55.6)		SHC1089	—
	2.19"-2.31"	(55.6-58.7)		SHC1090	—
	2.31"-2.44"	(58.7-61.9)		SHC1091	—
3	2.44"-2.63"	(61.9-66.7)	F8	SHC1092	—
	2.63"-2.81"	(66.7-71.4)		SHC1093	—
	2.81"-3.00"	(71.4-76.2)		SHC1094	—
	3.00"-3.25"	(76.2-82.5)		SHC1095**	—

Note: * IP66 Suitability when used with optional metal clad O-ring.

** Cable jacket may have to be stripped to pass through connector body.

Form 4 aluminum and plated steel nuts are machined, bodies are cast aluminum.

F5 and larger will not be colour coded.



Cast Aluminum



Cast Aluminum
Malleable Iron



45° MALE CORD CONNECTORS

IP66*
SUITABILITY



UL Listed to Type 4,
4X, 12 and Type 13

45° Male

N.P.T. Hub Size	Cord Diameter		Form Size	Colour Code	Machined Aluminum†	Machined Zinc-Plated SteelΔ	Cast Aluminum
Inches	(mm)						
1/2	.19"–.25"	(4.7–6.3)	F2	Red	VHC1021	—	—
	.25"–.38"	(6.3–9.7)		White	VHC1022	VHC1022ZP	—
	.38"–.50"	(9.7–12.7)		Blue	VHC1023	VHC1023ZP	—
	.50"–.63"	(12.7–15.9)		Brown	VHC1024**	VHC1024ZP**	—
3/4	.38"–.50"	(9.7–12.7)	F3	Blue	VHC1035	—	—
	.50"–.63"	(12.7–15.9)		Brown	VHC1036	—	—
	.63"–.75"	(15.9–19.0)		Yellow	VHC1037**	—	—
1	.63"–.75"	(15.9–19.0)	F4	Yellow	VHC1041	—	—
	.75"–.88"	(19.0–22.2)		Orchid	VHC1042	—	—
1–1/4	1.00"–1.13"	(25.4–28.6)	F5		—	—	VHC1052
	1.13"–1.25"	(28.6–31.7)			—	—	VHC1053**

Note: * IP66 Suitability when used with optional metal clad O-ring.

** Cable jacket may have to be stripped to pass through connector body.

Form 4 aluminum and plated steel nuts are machined, bodies are cast aluminum.

† Nuts are machined aluminum and bodies are cast aluminum.

Δ Nuts are machined zinc-plated steel and bodies are malleable iron, cadmium plated.



Machined
Aluminum †



Machined
Zinc-Plated Steel Δ



Cast Aluminum

90° MALE CORD CONNECTORS

E5

IP66*
SUITABILITY



UL Listed to Type 4,
4X, 12 and Type 13



90° Male

N.P.T. Hub Size	Cord Diameter Inches (mm)	Form Size	Colour Code	Machined Aluminum†	Machined Zinc-Plated Steel ^Δ	Nylon Gray	Nylon Black	Cast Aluminum
3/8	.25"–.31" (6.3–7.9)	F1	Black	NHC1010	—	—	—	—
	.31"–.38" (7.9–9.5)		White	NHC1011	—	—	—	—
	.38"–.44" (9.5–11.0)		Blue	NHC1012	—	—	—	—
1/2	.06"–.13" (1.6–3.2)	F2	Green	—	—	—	—	—
	.13"–.19" (3.2–4.7)		Orange	NHC1020	—	NHC1020CR	—	—
	.19"–.25" (4.7–6.3)		Red	NHC1021	NHC1021ZP	NHC1021CR	—	—
	.25"–.38" (6.3–9.7)		White	NHC1022	NHC1022ZP	NHC1022CR	NHC2022CR	—
	.38"–.50" (9.7–12.7)		Blue	NHC1023	NHC1023ZP	NHC1023CR	NHC2023CR	—
	.50"–.63" (12.7–15.9)		Brown	NHC1024**	NHC1024ZP**	NHC1024CR**	NHC2024CR**	—
	.38"–.50" (9.7–12.7)		Blue	NHC1035	NHC1035ZP	NHC1035CR	—	—
3/4	.50"–.63" (12.7–15.9)	F3	Brown	NHC1036	NHC1036ZP	NHC1036CR	—	—
	.63"–.75" (15.9–19.0)		Yellow	NHC1037	NHC1037ZP	NHC1037CR	—	—
	.75"–.88" (19.0–22.2)		Orchid	NHC1038	NHC1038ZP	NHC1038CR	—	—
	.50"–.63" (12.7–15.9)		Brown	NHC1040	—	—	—	—
1	.63"–.75" (15.9–19.0)	F4	Yellow	NHC1041	NHC1041ZP	NHC1041CR	NHC2041CR	—
	.75"–.88" (19.0–22.2)		Orchid	NHC1042	—	NHC1042CR	NHC2042CR**	—
	.88"–1.00" (22.2–25.4)		Gray	NHC1043**	—	NHC1043CR	NHC2043CR**	—
	1.00"–1.13" (25.4–28.7)		Pink	NHC1044**	—	—	—	—
	.88"–1.00" (22.2–25.4)		—	—	—	—	—	NHC1051
1–1/4	1.00"–1.13" (25.4–28.6)	F5	—	—	—	—	—	NHC1052
	1.13"–1.25" (28.6–31.7)		—	—	—	—	—	NHC1053**
	1.25"–1.38" (31.7–34.9)		—	—	—	—	—	NHC1054**
	1.00"–1.13" (25.4–28.6)		—	—	—	—	—	NHC1057
1–1/2	1.13"–1.25" (28.6–31.7)	F5	—	—	—	—	—	—
	1.25"–1.38" (31.7–34.9)		—	—	—	—	—	NHC1059
	1.38"–1.50" (34.9–38.1)		—	—	—	—	—	NHC1066

Note: * IP66 Suitability when used with optional metal clad O-ring.

** Cable jacket may have to be stripped to pass through connector body.

† Nuts are machined aluminum and bodies are cast aluminum.

Δ Compression nuts are machined zinc-plated steel and bodies are zinc-plated malleable iron.



Machined Aluminum†



Machined Zinc-Plated Steel^Δ



Gray Nylon



Black Nylon



Cast Aluminum



STRAIGHT FEMALE, UNDERGROUND FEEDER AND METRIC CONNECTORS



Straight Female

N.P.T. Hub Size	Cord Diameter		Form Size	Colour Code	Machined Aluminum
Inches	(mm)				
1/2	.25"-.38"	(6.3-9.7)	F2	White	FHC1022
	.38"-.50"	(9.7-12.7)		Blue	FHC1023
3/4	.38"-.50"	(9.7-12.7)	F2	Blue	FHC1033
	.50"-.63"	(12.7-15.9)		Brown	FHC1034
1	.75"-.88"	(19.0-22.2)	F4	Orchid	FHC1042†
	.88"-1.00"	(22.2-25.4)		Gray	FHC1043†

Note: * Cable jacket may have to be stripped to pass through connector body.
† Nuts are machined aluminum and bodies are cast aluminum.



Machined Aluminum



Underground Feeder Connectors

IP66*
SUITABILITY

N.P.T. Hub Size	Diameter		Wire Size	UF** Machined Aluminum	Zinc-Plated Steel	Machined Nylon Gray	Nylon Black
Inches	(mm)						
1/2	.2"x.4" min	(5.1 x 10.2)	2 # 14,	UFC0001	UFC0001ZP	UFC0001CR	UFC2001CR
	.25"-.55" max	(6.3 x 14.0)	2 # 12, 2 # 10.				
3/4	.2"x.4" min	(5.1x10.2)	2 # 14,	UFC0002	—	—	—
	.25"-.55" max	(6.3x14.0)	2 # 12, 2 # 10.				
3/4	.2"x.6" min	(5.1x15.2)	3 # 14,	UFC0003	—	UFC0003CR	UFC2003CR
	.26"x.78" max	(6.6x19.8)	3 # 12, 3 # 10.				

Note: * IP66 Suitability when used with optional metal clad O-ring.
** Wire sizes vary among manufacturers.



Machined Aluminum



Machined Zinc-Plated Steel



UL Listed to Type 4,
4X, 12 and Type 13

Metric Aluminum Cord Connectors

Hub Size	Cord Diameter		Form Size	Catalog Number
Inches	(mm)			
M16	.31"-.38"	(7.9-9.7)	F1	SHCM161011
M20	.31"-.38"	(7.9-9.7)	F1	SHCM201017
	.25"-.38"	(6.3-9.7)		SHCM201022
M20	.38"-.50"	(9.7-12.7)	F2	SHCM201023
	.50"-.62"	(12.7-15.8)		SHCM201024
M25	.38"-.50"	(9.7-12.7)	F2	SHCM251033
	.50"-.62"	(12.7-15.8)		SHCM251034
M30	.63"-.75"	(15.9-19.0)	F3	SHCM301037

Note: † When used with metal clad O-ring.
Non-metallic Locknuts sold separately.



Gray Nylon



Machined Aluminum

LOW PROFILE N.P.T., PG AND METRIC THREAD CONNECTORS

IP66*
SUITABILITY



SEC100BA

Low Profile N.P.T. Cord Connectors

N.P.T. Hub Size	Inches	Cord Diameter (mm)	Colour	Catalog Number	Non-metallic Locknuts
3/8	.18"-.31"	(4.6-7.9)	Gray	SEC38GA*	31622002LPK50
3/8	.18"-.31"	(4.6-7.9)	Black	SEC38BA*	31622002LPK50
1/2	.17"-.45"	(4.3-11.4)	Gray	SEC50GA	31622003LPK50
1/2	.17"-.45"	(4.3-11.4)	Black	SEC50BA	31622003LPK50
3/4	.45"-.71"	(11.4-18.0)	Gray	SEC75GA	31622007LPK50
3/4	.45"-.71"	(11.4-18.0)	Black	SEC75BA	31622007LPK50
1	.59"-1.00"	(15-25.4)	Gray	SEC100GA	31622008LPK50
1	.59"-1.00"	(15-25.4)	Black	SEC100BA	31622008LPK50

Note: Catalog numbers with "PK50" suffix are bulk packed 50 pieces.



SECP29GA

Low Profile PG△ Cord Connectors

Hub Size	Cord Diameter Inches	Cord Diameter (mm)	Colour	Catalog Number	Non-metallic Locknuts
PG7	.11"-.25"	(2.9-6.4)	Gray	SECP7GA*	LNP7BPK100
PG7	.11"-.25"	(2.9-6.4)	Black	SECP7BA*	LNP7BPK100
PG9	.18"-.31"	(4.6-7.9)	Gray	SECP9GA*	LNP9BPK100
PG9	.18"-.31"	(4.6-7.9)	Black	SECP9BA*	LNP9BPK100
PG11	.23"-.40"	(5.8-10.0)	Gray	SECP11GA*	LNP11BPK100
PG11	.23"-.40"	(5.8-10.0)	Black	SECP11BA*	LNP11BPK100
PG13.5	.17"-.47"	(4.3-11.9)	Gray	SECP13GA	LNP13BPK100
PG13.5	.17"-.47"	(4.3-11.9)	Black	SECP13BA	LNP13BPK100
PG16	.23"-.53"	(5.8-13.5)	Gray	SECP16GA	LNP16BPK100
PG16	.23"-.53"	(5.8-13.5)	Black	SECP16BA	LNP16BPK100
PG21	.45"-.71"	(11.4-17.9)	Gray	SECP21GA	LNP21BPK100
PG21	.45"-.71"	(11.4-17.9)	Black	SECP21BA	LNP21BPK100
PG29	.59"-.99"	(15-25.2)	Gray	SECP29GA	LNP29BPK25
PG29	.59"-.99"	(15-25.2)	Black	SECP29BA	LNP29BPK25
PG36	.88"-1.30"	(22.2-32.0)	Gray	SECP36GA	LNP36BPK25
PG36	.88"-1.30"	(22.2-32.0)	Black	SECP36BA	LNP36BPK25



LNP29BPK25

Low Profile Metric Cord Connectors

Hub Size	Cord Diameter Inches	Cord Diameter (mm)	Colour	Catalog Number	Non-metallic Locknuts
M12	.12"-.25"	(2.9-6.4)	Gray	SECM12G	LNM12BPK100
M12	.12"-.25"	(2.9-6.4)	Black	SECM12B	LNM12BPK100
M16	.11"-.31"	(2.7-7.9)	Gray	SECM16G	LNM16BPK100
M16	.11"-.31"	(2.7-7.9)	Black	SECM16B	LNM16BPK100
M20	.17"-.45"	(4.3-11.4)	Gray	SECM20G*	LNM20BPK100
M20	.17"-.45"	(4.3-11.4)	Black	SECM20B*	LNM20BPK100
M25	.49"-.71"	(12.3-18.0)	Gray	SECM25G*	LNM25BPK100
M25	.49"-.71"	(12.3-18.0)	Black	SECM25B*	LNM25BPK100
M32	.59"-1.00"	(15.0-25.4)	Gray	SECM32G*	LNM32BPK100
M32	.59"-1.00"	(15.0-25.4)	Black	SECM32B*	LNM32BPK100
M40	.87"-1.30"	(22.0-32.0)	Gray	SECM40G	LNM40BPK100
M40	.87"-1.30"	(22.0-32.0)	Black	SECM40B	LNM40BPK100

Note: Catalog numbers above with "PK100" suffix, i.e. LNP7BPK100, are bulk packed 100 per carton.

Catalog numbers above with "PK25" suffix, i.e. LNP29BPK25, are bulk packed 25 per carton.

* Items indicated are UL recognized components.

△ Panzergewinde.



ACCESSORIES

Locknuts — Non-Metallic

N.P.T. Hub Size	Catalog Number
1/4	31622001LPK50
3/8	31622002LPK50
1/2	31622003LPK50
3/4	31622007LPK50
1	31622008LPK50
1-1/4	—
1-1/2	—

*Note: Catalog numbers above with "PK50" suffix are bulk packed 50 per carton.
See page T-101 for additional technical data and dimensional drawings.*



Non-Metallic Locknuts

Metal Clad Sealing O-Rings

N.P.T. Hub Size	Catalog Number
1/2	20509001
3/4	20509002
1	20509003
1-1/4	20509004
1-1/2	20509005
2	20509006
2-1/2	20509007
3	20509008

Metal Clad
Sealing O-Rings

HUBBELL JUNIORS® MINIATURE NYLON CORD CONNECTORS

E9

WIRE MANAGEMENT

Miniature Nylon Cord Connector

N.P.T. Hub Size	Cord Diameter Range		Gray	Black
Inches	(mm)			
1/4	.08"–.14"	(1.9–3.4)	HJ1001GPK25	HJ1001BPK25
	.14"–.20"	(3.4–5.1)	HJ1002GPK25	HJ1002BPK25
	.20"–.27"	(5.1–6.7)	HJ1003GPK25	HJ1003BPK25
3/8	.15"–.21"	(3.7–5.3)	HJ1004GPK25	HJ1004BPK25
	.21"–.28"	(5.3–7.0)	HJ1005GPK25	HJ1005BPK25
	.28"–.34"	(7.0–8.6)	HJ1006GPK25	HJ1006BPK25
1/2	.06"–.13"	(1.6–3.2)	HJ1055GPK25	HJ1055BPK25
	.13"–.19"	(3.2–4.7)	HJ1056GPK25	HJ1056BPK25
	.19"–.25"	(4.7–6.3)	HJ1057GPK25	HJ1057BPK25
	.25"–.31"	(6.3–7.9)	HJ1058GPK25	HJ1058BPK25
	.31"–.38"	(7.9–9.5)	HJ1059GPK25	HJ1059BPK25
	.38"–.44"	(9.5–11.1)	HJ1060GPK25	HJ1060BPK25

Miniature Nylon Cord Connector with Spiral

N.P.T. Hub Size	Cord Diameter Range		Gray	Black
Inches	(mm)			
1/4	.08"–.14"	(1.9–3.4)	HJ1010GPK25	HJ1010BPK25
	.14"–.20"	(3.4–5.1)	HJ1011GPK25	HJ1011BPK25
	.20"–.27"	(5.1–6.7)	HJ1012GPK25	HJ1012BPK25
3/8	.15"–.21"	(3.7–5.3)	HJ1013GPK25	HJ1013BPK25
	.21"–.28"	(5.3–7.0)	HJ1014GPK25	HJ1014BPK25
	.28"–.34"	(7.0–8.6)	HJ1015GPK25	HJ1015BPK25
1/2	.13"–.19"	(3.2–4.7)	HJ1038GPK25	HJ1038BPK25
	.19"–.25"	(4.7–6.3)	HJ1039GPK25	HJ1039BPK25
	.25"–.31"	(6.3–7.9)	HJ1040GPK25	HJ1040BPK25
	.31"–.38"	(7.9–9.5)	HJ1041GPK25	HJ1041BPK25
	.38"–.44"	(9.5–11.1)	HJ1042GPK25	HJ1042BPK25
	.45"–.71"	(11.4–18.0)	HJ1044GPK25*	HJ1044BPK25*

Miniature Nylon Snap-In Cord Connector with Spiral

Cord Diameter Range		For Chassis	Gray	Black
Inches	(mm)	Thickness		
.22"–.27"	(5.6–6.9)	.10" (2.5) Max	HS1001GPK25	HS1001BPK25
.28"–.32"	(7.1–8.1)	.10" (2.5) Max	HS1002GPK25	HS1002BPK25
.30"–.36"	(7.6–9.1)	.13" (3.2) Max	HS1003GPK25	HS1003BPK25
.32"–.43"	(8.1–10.9)	.13" (3.2) Max	HS1004GPK25	HS1004BPK25

Note: Catalog numbers above with "PK25" suffix, i.e. HJ1001GPK25, are bulk packed 25 per carton.



Gray Cord Connector



Black Cord Connector



Gray Cord Connector with Spiral



Black Cord Connector with Spiral



Gray Snap-In Cord Connector



Black Snap-In Cord Connector



POLYTUFF® I NON-METALLIC LIQUIDTIGHT CONDUIT


PolyTuff® I Conduit–Gray

Rigid PVC core bonded to flexible PVC jacket

All nonmetallic construction ends metal fatigue and separation problems

UL Listed and CSA Certified

Cuts cleanly with a knife or PVC cutter so there are no jagged metal edges



IP66
SUITABILITY

PolyTuff® I Conduit

Trade Size (metric designator)	Feet (m)	Catalog Number
¾ (12)	100 (30.5)	G1038
½ (16)	100 (30.5)	G1050
¾ (21)	100 (30.5)	G1075
1 (27)	100 (30.5)	G1100
1¼ (35)	100 (30.5)	G1125
1½ (41)	50 (15.2)	G1150
2 (53)	50 (15.2)	G1200

POLYTUFF® II NON-METALLIC LIQUIDTIGHT TUBING

E11

WIRE MANAGEMENT

PolyTuff® II Tubing-Black

PVC core with corrugated walls bonded to PVC jacket

Handles twists, turns, bends, switchbacks and straightaways with ease

All nonmetallic construction ends fatigue and separation problems

Can be cut with a knife or PVC cutters

UL Recognized and CSA Certified



IP66
SUITABILITY

PolyTuff® II Tubing

Trade Size (metric designator)	Feet (m)	Catalog Number
¼ (10)	100 (30.5)	B2025
⅜ (12)	100 (30.5)	B2038
½ (16)	100 (30.5)	B2050
¾ (21)	100 (30.5)	B2075
1 (27)	100 (30.5)	B2100
1¼ (35)	100 (30.5)	B2125
1½ (41)	50 (15.2)	B2150
2 (53)	50 (15.2)	B2200



POLYTUFF® II NON-METALLIC LIQUIDTIGHT FITTINGS



UL Listed to Type 4,
4X, 12 and Type 13

Straight with Male Non-Metallic Liquidtight Fittings

Trade Size (metric designator)	Black Catalog Number	Gray Catalog Number
¼ (6)	F2025	—
⅜ (9)	P038NBKA	P038NGYA
½ (13)	P050NBKA	P050NGYA
¾ (19)	P075NBKA	P075NGYA
1 (25)	P100NBKA	P100NGYA
1¼ (32)	P125NBK	P125NGY
1½ (38)	P150NBK	P150NGY
2 (51)	P200NBK	P200NGY

Note: Fittings are to be used with PolyTuff I and PolyTuff II.

¾" Liquidtight conduit fitting have ½ N.P.T. male threads.



P075NGYA



P125NGY

SwivelLok® Multi-Position with Male Non-Metallic Liquidtight Fittings

Trade Size (metric designator)	Black Catalog Number	Gray Catalog Number
⅜ (9)	PS0389NBK	PS0389NGY
½ (13)	PS0509NBK	PS0509NGY
¾ (19)	PS0759NBK	PS0759NGY
1 (25)	PS1009NBK	PS1009NGY

Note: Fittings are to be used with PolyTuff I and PolyTuff II.

¾" Liquidtight conduit fitting have ½ N.P.T. male threads.



PS0509NGY – SwivelLok®

Fixed 90° Fittings for Non-Metallic Conduit

Trade Size (metric designator)	Black Catalog Number	Gray Catalog Number
¼ (6)	F20259	—
⅜ (9)	P0389NBK	P0389NGY
½ (13)	P0509NBK	P0509NGY
¾ (19)	P0759NBK	P0759NGY
1 (25)	P1009NBK	P1009NGY
1¼ (32)	P1259NBK	P1259NGY

Note: Fittings are to be used with PolyTuff I and PolyTuff II.

¾" Liquidtight conduit fitting have ½ N.P.T. male threads.



P1259NGY

SwivelLok® Flexible Conduit Kit

Trade Size (metric designator)	Fitting and Conduit	Catalog Number
½ (13)	2 PS0509NGY, 6' G1050	PS05GYKIT
¾ (19)	2 PS0759NGY, 6' G1075	PS07GYKIT



PS05GYKIT