






LOC		DIST		P	F	REVISIONS				
BD	48	ZONE	LTR			DESCRIPTION	DATE	APPD		
			O			RELEASED	-	-	-	
			A			REVISED PER ECN-2422	8/24/88	SW		
			B			REVISED PER ECN BD5388	11/27/91	RM		
			C			REV PER EC 0020-117-93	03/17/93	SB		
			C1			ADDED -6, -7, -8 PER NPR 4841	07/09/93	MW		
			D			REV PER EC 0020-1344-93	11/01/93	SB		
			E			OBSOLETE -6 THRU -8 PER EC 0420-141-96	25 SEPT 97	SB		



1. PARTS PACKAGED UNASSEMBLED AS A UNIT KIT.
CABLE CLAMP HALVES: BLACK ABS MOLDING COMPOUND, FILLISTER HEAD SCREWS, HEX NUTS & MOUNTING SCREWS: STEEL PER ASTM A108, GROMMETS: FLEXIBLE PVC, UL 94V-0 RATED, COLOR: BLACK.
CABLE CLAMP HALVES: NICKEL OVER COPPER, FILLISTER HEAD SCREWS, HEX NUTS & MOUNTING SCREWS: ZINC PLATED PER ASTM B633, TYPE III, CLASS SC1, CLEAR CHROMATE.



GROMMET ASSORTMENT
FOR SIZES 1 & 2 ONLY



GROMMET ASSORTMENT
FOR SIZES 3, 4 & 5 ONLY

OBSOLETE	SMALL PACK	.680	.640	2.090	1.920	1.852	3	748677-8
OBSOLETE	SMALL PACK	.620	.620	1.545	1.910	1.312	2	748677-7
OBSOLETE	SMALL PACK	.570	.630	1.215	1.910	.984	1	748677-6
	STANDARD	.900	.730	2.644	1.920	2.406	5	748677-5
	STANDARD	.800	.620	2.738	1.920	2.500	4	748677-4
	STANDARD	.680	.640	2.090	1.920	1.852	3	748677-3
	STANDARD	.620	.620	1.545	1.910	1.312	2	748677-2
	STANDARD	.570	.630	1.215	1.910	.984	1	748677-1
	PACKAGING	E	D	C	B	A	SIZE	PART NO
	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± - MATERIAL 2		DR 5/4/88 S.WELDON		AMP AMP INCORPORATED Harrisburg, Pa. 17105 NAME KIT, CABLE CLAMP, 180° EXIT, W/GROMMETS, PLATED PLASTIC, AMPLIMITE®			
CHK 5/4/88 W.G.LENKER								
APPD 5/6/88 R.WHYNE								
			APPD 5/6/88 V.KUMAR		DRAWING NO 748677			
		PRODUCT SPEC -						
FINISH 3		APPLICATION SPEC -		SIZE D	FSCM NO 00779	SHEET 1 OF 1		
		WEIGHT -		SCALE 3:1				