








Dimensions: mm (In.)



101-0362-EV



101-0462-EV



Electrical Specifications:

- Rating: 50mA/12VDC
- Insulation resistance: 100MΩ min. @ 250VDC
- Dielectric Strength: 250VAC 1 minute
- Contact resistance: <100mΩ
- Electrical life: 300,000 cycles

Mechanical Specifications:

- Mechanical life: 500,000 cycles
- Operating temperature: -25°C to +70°C
- Operating force: 130 ±50gf

Note:

- H: .276 (101-0362-EV), .374 (101-0462-EV)
- RoHS Compliant

Material:

- Contact: phosphor bronze plated silver

Tactile Switches (Thru-Hole)
101-0362-EV, 101-0462-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[101-0362-EV](#) [101-0462-EV](#)