

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL INTERNATIONAL RIGHTS RESERVED.

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		A	REVISED PER ECO-10-013617	26JUL10	HMR	CR

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: TIN PLATED, COPPER ALLOY.
SCREWS: 6-32, ZINC PLATED STEEL.

ELECTRICAL:
UL/CSA:
CLASS C: 20A, 300V.
CLASS D: 5A, 600V.
WIRE RANGE: 12-22 AWG.

MECHANICAL:
RECOMMENDED TORQUE: 7 IN-LB.
OPERATING TEMP.: 105°C MAX

- 1SCREWS ARE NICKEL PLATED BRASS.
- 2PRELIMINARY PART NUMBER.



9.436	25	JC6-E108-25	2-1546721-5
9.061	24	JC6-E108-24	2-1546721-4
8.686	23	JC6-E108-23	2-1546721-3
8.311	22	JC6-E108-22	2-1546721-2
7.936	21	JC6-E108-21	2-1546721-1
7.561	20	JC6-E108-20	2-1546721-0
7.186	19	JC6-E108-19	1-1546721-9
6.811	18	JC6-E108-18	1-1546721-8
6.436	17	JC6-E108-17	1-1546721-7
6.061	16	JC6-E108-16	1-1546721-6
5.686	15	JC6-E108-15	1-1546721-5
5.311	14	JC6-E108-14	1-1546721-4
4.936	13	JC6-E108-13	1-1546721-3
4.561	12	JC6-E108-12	1-1546721-2
4.186	11	JC6-E108-11	1-1546721-1
3.811	10	JC6-E108-10	1-1546721-0
3.436	9	JC6-E108-09	1546721-9
3.061	8	JC6-E108-08	1546721-8
2.686	7	JC6-E108-07	1546721-7
2.311	6	JC6-E108-06	1546721-6
1.936	5	JC6-E108-05	1546721-5
1.561	4	JC6-E108-04	1546721-4
1.186	3	JC6-E106-03	2-1546721-6
1.186	3	JC6-E108-03	1546721-3
.811	2	JC6-E108-02	1546721-2
DIM. A	NO. OF POS.	CATALOG NUMBER	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 12/8/04	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK S. YODER 12/8/04				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. YODER 12/8/04	NAME		
	0 PLC ± -		PRODUCT SPEC	JC6-E108-XX ASSEMBLY		
	1 PLC ± -		APPLICATION SPEC			
MATERIAL		FINISH	WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-1546721
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV A	