




Flaretek® PFA

Straight Adapter, MNPT

[Ordering Information](#) | [Accessories](#) | [Technical Information](#)

[Click to enlarge](#)

CAD You have the ability to access 3D and 2D product data that is compatible with today's CAD modeling packages. To decrease system design time, simply download parts directly into your design.

Ordering Information

Part Number	Nut Option	O.D. Tube Size	MNPT Size	Orifice	Dimensions			Hex	Quantity	
					A	B	C			
C4-2FN-*	PVDF (1)	1/4"	1/8"	0.13" (3.3 mm)	1.93" (49.0 mm)	1.09" (27.7 mm)	0.55" (14.0 mm)	5/8"	1	ADD TO CART
C4-4FN-*	PVDF (1)	1/4"	1/4"	0.13" (3.3 mm)	1.93" (49.0 mm)	1.09" (27.7 mm)	0.55" (14.0 mm)	5/8"	1	ADD TO CART
C4-6FN-*	PVDF (1)	1/4"	3/8"	0.13" (3.3 mm)	1.93" (49.0 mm)	1.09" (27.7 mm)	0.55" (14.0 mm)	11/16"	1	ADD TO CART
C4-8FN-*	PVDF (1)	1/4"	1/2"	0.13" (3.3 mm)	2.03" (51.6 mm)	1.09" (27.7 mm)	0.66" (16.8 mm)	13/16"	1	ADD TO CART
C6-2FN-*	PVDF (1)	3/8"	1/8"	0.20" (5.1 mm)	2.04" (51.8 mm)	1.21" (30.7 mm)	0.55" (14.0 mm)	13/16"	1	ADD TO CART
C6-4FN-*	PVDF (1)	3/8"	1/4"	0.25" (6.4 mm)	2.04" (51.8 mm)	1.21" (30.7 mm)	0.55" (14.0 mm)	13/16"	1	ADD TO CART
C6-6FN-*	PVDF (1)	3/8"	3/8"	0.25" (6.4 mm)	2.04" (51.8 mm)	1.21" (30.7 mm)	0.55" (14.0 mm)	13/16"	1	ADD TO CART
C6-8FN-*	PVDF (1)	3/8"	1/2"	0.25" (6.4 mm)	2.15" (54.6 mm)	1.21" (30.7 mm)	0.66" (16.8 mm)	15/16"	1	ADD TO CART
C6-12FN-*	PVDF (1)	3/8"	3/4"	0.25" (6.4 mm)	2.16" (54.9 mm)	1.21" (30.7 mm)	0.67" (17.0 mm)	1 3/16"	1	ADD TO CART
C8-2FN-*	PVDF (1)	1/2"	1/8"	0.20" (5.1 mm)	2.14" (54.4 mm)	1.31" (33.3 mm)	0.55" (14.0 mm)	15/16"	1	ADD TO CART
C8-4FN-*	PVDF (1)	1/2"	1/4"	0.28" (7.1 mm)	2.15" (54.6 mm)	1.31" (33.3 mm)	0.55" (14.0 mm)	15/16"	1	ADD TO CART
C8-6FN-*	PVDF (1)	1/2"	3/8"	0.38" (9.7 mm)	2.15" (54.6 mm)	1.31" (33.3 mm)	0.55" (14.0 mm)	15/16"	1	ADD TO CART
C8-8FN-*	PVDF (1)	1/2"	1/2"	0.38" (9.7 mm)	2.25" (57.2 mm)	1.31" (33.3 mm)	0.66" (16.8 mm)	15/16"	1	ADD TO CART
C8-12FN-*	PVDF (1)	1/2"	3/4"	0.38" (9.7 mm)	2.26" (57.4 mm)	1.31" (33.3 mm)	0.67" (17.0 mm)	1 3/16"	1	ADD TO CART
C12-8FN-*	PVDF (1)	3/4"	1/2"	0.52" (13.2 mm)	2.44" (62.0 mm)	1.48" (37.6 mm)	0.66" (16.8 mm)	1 3/16"	1	ADD TO CART
C12-12FN-*	PVDF (1)	3/4"	3/4"	0.63" (16.0 mm)	2.44" (62.0 mm)	1.48" (37.6 mm)	0.67" (17.0 mm)	1 3/16"	1	ADD TO CART
C12-16FN-*	PVDF (1)	3/4"	1"	0.63" (16.0 mm)	2.65" (67.3 mm)	1.52" (38.6 mm)	0.85" (21.6 mm)	1 7/16"	1	ADD TO CART
C16-12FN-*	PVDF (1)	1"	3/4"	0.66" (16.8 mm)	2.68" (68.1 mm)	1.72" (43.7 mm)	0.67" (17.0 mm)	1 7/16"	1	ADD TO CART
C16-16FN-*	PVDF (1)	1"	1"	0.88" (22.4 mm)	2.84" (72.1 mm)	1.72" (43.7 mm)	0.85" (21.6 mm)	1 7/16"	1	ADD TO CART

Accessories

- Flare Fitting Assembly Aids, Wrenches
- Flaretek® Fitting Flaring Tools
- PrimeLock® and Flaretek® Heating Tools
- Torque Verification Device for 1/4", 3/8", 1/2", 3/4" or 1" fitting connections
- Tube Cutters

Technical Information

- Ultrapure Flare Style PFA Tube Fittings Flaretek® Ultrapure PFA Tube Fittings
- Flaretek® Tube Fitting Flare and Assembly Procedures for 1/4", 3/8", 1/2", 3/4" and 1" sizes
- Maximum Pressure Capabilities

[View printer-friendly version of this page](#)

