

1 AC outlet, direct plug-in surge suppressor with built-in tel/modem surge protection

MODEL NUMBER: TRAVELCUBE



Description

The TRAVELCUBE is designed for convenient portable and economical surge protection. Small and powerful, the TRAVELCUBE features 540 joules and carries \$10K of insurance as well as a . Throw it in a briefcase or purse and have quality surge protection wherever you need it — hotel room, dorm, client office — anywhere!

Features

- Portable wall-mount cube stores easily in any bag or briefcase
- 1 NEMA5-15R AC outlet
- 540 joules of protection shields equipment from harmful surges, spikes and line noise
- Diagnostic LED displays protection status
- Built-in tel/modem surge protection
- Bonus 6-ft. phone cord included
- UL 1449 rated 3rd Edition
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
Intended Application	Home/Office; Travel
Style	Direct Plug-in
OUTPUT	
Frequency Compatibility	50 / 60 Hz

Highlights

- 1 AC outlet
- Direct plug-in design
- Built-in tel/modem surge protection
- 540 joule rating
- Diagnostic LED displays protection status
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for use with laptops, fax machines, electronic notepads, personal organizers and other portable electronic devices

Package Includes

- TRAVELCUBE surge suppressor
- Bonus 6-ft. telephone cord

Output (Watts)	1800
Circuit Breaker (amps)	15
Outlet Quantity / Type	1 NEMA 5-15R
Number of Outlets	1
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	0
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	500V
EMI / RFI Filtering	Up to 20dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.83 x 5.12 x 6.50
Shipping Dimensions (hwd / cm)	7.19 x 13.00 x 16.51
Shipping Weight (lbs.)	.42
Shipping Weight (kg)	0.19

Unit Dimensions (hwd / in.)	1.49 x 2.16 x 3.07
Unit Dimensions (hwd / cm)	3.78 x 5.49 x 7.80
Unit Weight (lbs.)	.17
Unit Weight (kg)	0.08
Material of Construction	Plastic
Form Factors Supported	Direct plug in suppressor supports wall-mounting directly into AC receptacle

CERTIFICATIONS

UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
Approvals	Exceeds IEEE 587 category A&B specifications

WARRANTY

Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.