


**OBSOLETE- USE PLD-21N30PQ****Specifications**

|                                |                                                |
|--------------------------------|------------------------------------------------|
| Resonant Frequency (Hz)        | 3000 $\pm$ 500                                 |
| Operating Voltage (Vdc)        | 3 ~ 30                                         |
| Rated Voltage (Vdc)            | 12                                             |
| Current Consumption Max. (mA)  | 12 at Rated Voltage                            |
| Sound Pressure Level Min. (dB) | 80 at 30 cm at Rated Voltage                   |
| Tone/Pulse Rate (Hz)           | Constant + Slow Pulse 1.2 $\pm$ 20%            |
| Operating Temperature (°C)     | -20 ~ +70                                      |
| Storage Temperature (°C)       | -30 ~ +80                                      |
| Housing                        | ABS 777 UL94HB plastic resin<br>(Color: Black) |
| Leading Pins                   | Tin Plated Brass                               |
| Weight (Grams)                 | 3.0                                            |
| Options                        | For other options contact factory              |

**Dimensions:** (units: mm)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PLD-21N30P](#)