



Datasheet for part number MDM-21PH006P

Our Catalog Part Number: MDM-21PH006P			
Brand: Cannon	Product Category: Micro	Product Line: Micros	Series: MICRO

Product Datasheet	
Series	Micro "D" Metal Shell
Arrangement	21 Contact
Gender	Pin
Contact Material	gold plated copper alloy
Contact Typ	crimp
Contact Resistance	8 milliohms max.
Termination Type	36" Min, M16874/4 #26AWG, Colored Code
Shell Material	Aluminum
Shell Finish	Yellow Chromate/Cadmium over Nickel
Insulator Material	contact size 9 to100 = liquid crystalline polymer, contact arrangements 7C2 or 24C4 = Diallyl phthalate
Hardware	Jackpost (standard)
Coupling	Jackscrew Coupling
Current Rating	3 A max.
Dielectric Withstanding Voltage	600 VAC at sea level 150 VAC at 70,00' altitude
Insulator Resistance	5000 megohms min.
Thermal Shock	-55°/+125°
Physical Shock	50 G's, 3 axes, 6 milisecond duration sawtooth pulse
Vibration	20G's, 10-2000 Hz. 12 hours
Durability	500 cycles of mating and unmating, 500 CPH max.
Moisture Resistance	Insulator resistance > 100 megohms
SaltSpray	48 hours