

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

97-00-0450

Status:

Active

Overview:

KK® Interconnection System

Description:

KK® Cat Ear Crimp Terminal 4809, 22-30 AWG, Un-plated, Reel

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07 (PDF)

Product Specification PS-99020-0088 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Product Name

UPC

Crimp Terminals

4809

Signal

Yes

KK® Interconnection System

Cat Ear, KK®

822350245616

Physical

Gender

Material - Metal

Material - Plating Mating

Net Weight

Packaging Type

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

Brass

Unplated

0.068/g

Reel

Crimp or Compression

1.57mm max.

22, 24, 26, 28, 30

N/A

Material Info

Reference - Drawing Numbers

Product Specification

PS-10-07, PS-99020-0088



image - Reference onlySeries

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

4809Series

Use With

6471 2.54mm Pitch KK® Crimp Terminal Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Insertion Tool	0638120000
Mini-Mac™ for Cat Ear and Anti-Fish Hook Crimp Terminals, 22-30 AWG Wire	0638887100
Extraction Tool	0011030022
Terminator Die	0011402102

This document was generated on 02/11/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION