


HEAT SEALED



- 1.CABLE:NO UL,,28AWG(7/0.127),TINNED AND STRANDED COPPER WIRE
INSULATOR:PVC,ID:0.85mm ,CABLING:7C+DRAIN WIRE
SHIELD:AL/MY COVERAGE
JACKET:PVC,COMPLIANCE ROHS,COLOR:BEIGE,D.D:5mm
- 2.2PCS CONNECTOR:DB-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR
INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE
CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED
SHELL:NICKEL PLATED.
CONNECTOR COMPLIANCE ROHS
- 3.HOOD:PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER
ON INNER MOLD AND INJECTION OUTER MOLD WITH
THUMB SCREW#4-40 UNC
COLOR:BEIGE,COMPLIANCE ROHS
- 4 Fulfill ROHS Guideline
- 5 ELECTRONIC TEST
100% OPEN SHORT+MISS WIRE TEST

DRAWING

DB9PIN JACK(J1)	WIRE	DB9PIN JACK(J2)
2		3
3		2
4		6
5		5
6		4
7		8
8		7
SHELL	DRAIN WIRE	SHELL

PART NO	4070-XX	SHEET NO	1	THIRD ANGLE PROJECTION
TITLE	DB9 PIN FEMALE TO DB9 PIN MALE BEIGE COLOR	SCALE	N.T.S	DRAWN BY & DATE
		SIZE	A4	CHECKED BY & DATE
		UNIT		APPROVED BY & DATE
DWN NO	1219-05			