





| REV. | DESCRIPTION | DATE       |
|------|-------------|------------|
| A    | RELEASE     | 2012.11.12 |

NOTES:  
Insulator Material: Nylon-6T, UL 94V-0  
Contact Plating: TIN, 80-100 $\mu$ "  
Contact Material: Brass

Current Rating : 1A AC,DC  
Contact Resistance: 20M $\Omega$  Max.  
Dielectric Withstanding: AC 500V  
Insulator Resistance: 1000M $\Omega$  Min.  
Operating Temp.: -40°C~+105°C



| NUMBER<br>OF POSITIONS | DIMENSIONS |       |
|------------------------|------------|-------|
|                        | A          | B     |
| 06                     | 4.00       | 13.30 |
| 08                     | 6.00       | 15.30 |
| 10                     | 8.00       | 17.30 |
| 12                     | 10.00      | 19.30 |
| 14                     | 12.00      | 21.30 |
| 16                     | 14.00      | 23.30 |
| 18                     | 16.00      | 25.20 |
| 20                     | 18.00      | 27.30 |
| 24                     | 22.00      | 31.30 |
| 26                     | 24.00      | 33.30 |
| 30                     | 28.00      | 37.30 |
| 34                     | 32.00      | 41.30 |
| 40                     | 38.00      | 47.30 |
| 44                     | 42.00      | 51.30 |
| 50                     | 48.00      | 57.30 |
| 60                     | 58.00      | 67.30 |
| 64                     | 62.00      | 71.30 |



|                  |             |            |     |              |                 |        |
|------------------|-------------|------------|-----|--------------|-----------------|--------|
| UNLESS TOLERANCE |             | DRAW BY    |     | CnC Tech,LLC |                 |        |
| GENERAL          | ANGLE       | DESIGN BY  |     |              |                 |        |
| X. ± 0.30        | X.° ± 3.0°  | CHECK BY   |     |              |                 |        |
| .X ± 0.20        | .X° ± 2.0°  |            |     |              |                 |        |
| .XX ± 0.15       | .XX° ± 1.0° | APPROVE BY |     | Port NO.     | 3120-XX-0200-99 |        |
| .XXX ± 0.08      | .XXX ± 0.5° |            |     | SCALE        |                 | SHEET  |
|                  |             |            | 1:1 | 1/1          | MM              | REV: A |