




RECOMMENDED STRIP LENGTH

2	RG-217/U	1-51692-6 AMP	220065-1	X	9.53 [.375]	13.89 [.547]	23.42 [.922]	A	225982-2	225788-4	2221878-1	1-51692-6
	-	-	-	-	-	-	-	-	-	-	-	1-51692-5
	RG-217/U	11400158 AMP	220065-1	Y	9.53 [.375]	13.89 [.547]	23.42 [.922]	A	225982-2	225788-4	225981-1	1-51692-4
	RG-217	1-51692-1 AMP	220065-1	X	9.53 [.375]	13.89 [.547]	23.42 [.922]	A	225982-2	225788-4	225981-2	1-51692-1
SUPERSEDED BY 1-225092-0												
OBSOLETE OBSOLETE	-	-	-	-	-	-	-	A	-	-	-	51692-7
	RG-165	00779 M39012/01B0011 AMP & DATE CODE	220015-1	X	-	-	-	B	51713-2	51695-8	51701-1	51692-6
	RG-216	00779 M39012/01B0014 AMP & DATE CODE	220015-1	X	4.77 [.188]	12.70 [.500]	17.48 [.688]	A	51713-2	51695-6	51701-1	51692-5
	RG-11A,144	00779 M39012/01B0013 AMP & DATE CODE	220015-1	X	-	-	-	B	9-51713-4	51695-6	51701-1	51692-4
	-	-	-	-	-	-	-	-	-	-	-	51692-3
	RG-213	00779 M39012/01B0007 AMP & DATE CODE	220015-1	X	-	-	-	B	9-51713-4	51695-2	51701-1	51692-2
	RG-214	00779 M39012/01B0008 AMP & DATE CODE	220015-1	X	4.77 [.188]	12.70 [.500]	17.48 [.688]	A	9-51713-4	51695-2	51701-1	51692-1
	CABLE SIZE	STAMPING	CRIMPING TOOL	VIEW	E	D	C	DETAIL	3 FERRULE QTY=1	2 CONTACT QTY=1	1 PLUG ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.41 [.016]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN N. FRITZ 9-18-90
CHK M. SNEED 10-18-90
APVD -

PRODUCT SPEC 108-12019
APPLICATION SPEC -

SIZE A1
WEIGHT -

CUSTOMER DRAWING

TE Connectivity

PLUG, SERIES N -

SIZE CAGE CODE DRAWING NO
A1 00779 51692

RESTRICTED TO -

SCALE 4:1 SHEET 1 OF 1 REV T

4805 (3/11)