


Search for: in
[HOME](#) [COMPANY PROFILE](#) [PRODUCTS](#) [ENGINEERING AND DESIGN](#) [CUSTOM CABLE ASSEMBLIES](#) [CONTACT US](#)

Custom Cables

Custom Cables Off The Shelf

(of course this only represents a small portion of cable in stock)

[Print](#)

live support software for business

Part Number ▲	No. Of Cond.	AWG Size	Strand Const Mat.	Ins. Mat.	Shield Construction	Jacket Mat.	O.D.	Special Features
AS148.REV1	8	30	7/36 T.C.	FEP	38AWG T.C. BRAIDED	S.R.	.145	ECONOMICAL S.R. JACKETED CABLE
AS165.REV1	2	29	51/46 B.C.	S.R.	8-6-40 T.C. BRAIDED	S.R.	.095	ULTRA FLEXIBLE SHIELDED TWISTED PAIR
AS298	1	18	413/44S.P.C.			S.R.	.160"	HIGH TEMP, HIGH VOLTAGE
AS323.REV1	10	28	40/44 B.C.	FEP	NO SHIELD	S.R.	.120	HIGH TEMP FLEXIBLE CABLE, WHITE JACKET
AS363	10	28	40/44 B.C.	PVC	NO SHIELD	PVC	.130	ULTRA THIN PVC INSULATED CABLE.
CW2516.REV1	3	29	51/46 B.C.	FEP	8-5-40 T.C. SPIRAL	PVC	.080	UL20469 APPROVED BLACK JACKET
CW2517	4	32	25/46 B.C.	PVC	8-5-40 T.C. SPIRAL	PVC	.085	SMALL O.D. BLACK JACKET
CW2518	3	30	41/46 B.C.	PVC	8-5-40 T. C. SPIRAL	PVC	.073	UL APPROVED, SOFT DUROMETER PVC WHITE JACKET
CW3330	10	24	105/44 B.C.	PVC	24-9-30 T.C. BRAIDED	PU	.240	HIGHLY DURABLE POLYURETHANE CABLE, BLACK & GRAY IN STOCK
CW3416	10	28	40/44 B.C.	PVC	40AWG T.C. BRAIDED	PVC	.154	BLACK JACKET
CW3462 GRAY	4	26	65/44 S.P.C.	PFA	44AWG S.P.C.	S.R.	.173	PHACO STYLE CABLE
CW3625T	12	28	40/44 T.C.	PVC	40 AWG T.C. BRAIDED	PVC	.220	GRAY JACKET
CW5434.REV1	6	26	65/44 B.C.	PVC	SPIRAL T.C.	PVC	.163	FLEXIBLE MULTI- PURPOSE PVC CABLE
CW5663	3	24	105/44 S.P.C.	PFA	3 S.P.C. DRAIN WIRES	S.R.	.180	PHACO STYLE CABLE
CW5664	3	26	65/44 S.P.C.	PFA	3 S.P.C. DRAIN WIRES	S.R.	.119	PHACO STYLE CABLE
CW5765	10	28	40/44S.P.C.	PTFE	24-7-40S.P.C. BRAIDED	S.R.	.204	FIVE TWISTED PAIRS GRAY JACKET
CW6005	16	30	25/44 B.C.	PVC	40AWG T.C. BRAIDED	PVC	.157	VERY FLEXIBLE CABLE
CW6161	6	28	40/44B.C.	PVC	24-6-40 T.C. BRAIDED	PVC	.149	BARE COPPER DRAIN WIRE, WHITE JACKET.
CW6300	26	28	40/44B.C.	PVC	24-8-40T.C. BRAIDED	PVC	.214	HIGHLY FLEXIBLE
CW6407	4	30	25/44B.C.	S.R.	44 AWG T.C. SPIRAL	S.R.	0.121	ULTRA FLEXIBLE ALL S.R. CABLE
CW6424	37	28	40/44B.C.	PVC	40AWG T.C. BRAIDED	PVC	.245	HIGHLY FLEXIBLE MATTE GRAY JACKET
CW6461	10	24	105/44B.C.	PVC	48-6-40T.C. BRAIDED	PVC	.308	FIVE TWISTED PAIRS

Custom Cables

Custom Cables

► Custom Cables available off the shelf

► Hookup Wire

► Multiconductor Cable

► Flexible Power Cable

► Medical Cables


► Instrumentation

► Mini Coax

► Braided Wire

► Flexible Wire Rope

► Litz Wire



Custom Cables

Custom Cables available off the shelf

Hookup Wire

PVC Hookup Wire
Silicone Hookup Wire
FEP Hookup Wire
Polyurethane Hookup Wire

Multiconductor Cable

PVC Multiconductor Cable
Silicone Multiconductor Cable
FEP Multiconductor Cable

Flexible Power Cable

PVC Flexible Power Cable
Silicone Flexible Power Cable
PVC Ground Strap

Medical Cables

Hookup Wire
Multiconductor Cable

Instrumentation

Hookup Wire
Multiconductor Cable

Mini Coax

Mini Coax

Braided Wire

Tubular Braided Wire
Flat Braided Wire
Stainless Steel Braided Wire
PVC Ground Strap

Flexible Wire Rope

Wire Flexible Wire Rope

Litz Wire

Type 1
Type 2
Type 3
Type 4
Type 5
Type 6
Type 7
Type 8
Magnet Wire Tables

[Site Map](#) | [Contact Us](#) | [Products](#)



Call us 818-882-8311