



Copyright © 2012 - Explorer Cases by GT Line srl  
Via Del Lavoro, 50/52 - I - 40056 Crespellano (BOLOGNA) - ITALY  
Partita IVA IT696831205  
Telefono +39/051/65041 - Fax +39/051/734925  
vendite@gtline.com - Skype: gt.line.01  
[www.explorercases.com](http://www.explorercases.com)  
Page printed: 13/07/2012



## 4419 B

EAN 8024482015316

### Versions

|         |                   |
|---------|-------------------|
| 4419 B  | black w/foam      |
| 4419 BE | black empty       |
| 4419 G  | mil. green w/foam |
| 4419 GE | mil. green empty  |
| 4419 O  | orange w/foam     |
| 4419 OE | orange empty      |

### 4419 B - Copolymer polypropylene waterproof case

| Technical Features                                  |              | L                     | W                 | D                |               |              |
|-----------------------------------------------------|--------------|-----------------------|-------------------|------------------|---------------|--------------|
|                                                     |              | Length                | Width             | Depth            | Cover         | Bottom       |
| Internal dim.                                       | in           | 17 1/2                | 13 9/16           | 7 1/2            | 1 7/8         | 5 5/8        |
| External dim.                                       | in           | 18 11/16              | 16 5/16           | 8 7/16           |               |              |
| Weight empty                                        |              | lbs 8.81              |                   |                  |               |              |
| Weight w/foam                                       |              | lbs 10.36             |                   |                  |               |              |
| Weight w/multi                                      |              | lbs ---               |                   |                  |               |              |
| Volume                                              |              | gal 7.66              |                   |                  |               |              |
| Buoyancy                                            |              | lbs/max 7.66          |                   |                  |               |              |
| Temp. rating                                        |              | °F min -27.4 max +194 |                   |                  |               |              |
| Certifications                                      |              |                       |                   |                  |               |              |
| 2002/95/EC Conformity with the Directive 2002/95/EC |              |                       |                   |                  |               |              |
| DEF STAN 81-41 (level J)                            |              |                       |                   |                  |               |              |
| IP67 Dustproof - Waterproof                         |              |                       |                   |                  |               |              |
| STANAG 4280 (edition 2)                             |              |                       |                   |                  |               |              |
| Versions                                            | B            | BE                    | G                 | GE               | O             | OE           |
|                                                     | black w/foam | black empty           | mil. green w/foam | mil. green empty | orange w/foam | orange empty |



