

**Mallory Sonalert Products, Inc.**



Part #:

**SC110FJ****Sales Outline Drawing**

Revision:

**B****Specifications:**

|                       |  |
|-----------------------|--|
| Sound Level Category  | Soft   |
| Mode of Operation     | Slow Pulse @ 0.5 - 2.5 PPS   |
| Voltage Rating        | 30 to 120 VAC/DC   |
| Frequency             | 2900 ± 500 Hz  |
| Loudness @ 2 FT       | 64 to 77 dB(A) Typ.  |
| Loudness @ Min Vdc    | 55/65 dB(A) @ 2 Feet and 30 Vdc  |
| Loudness @ Max Vdc    | 65/78 dB(A) @ 2 Feet and 120 Vdc   |
| Current Draw          | 4-13 mA  |
| Duty Cycle (%)        | 50   |
| Housing Material      | 6/6 Nylon, Color: Black  |
| Storage Temperature   | -40° to +85° C   |
| Operating Temperature | -30° to +65° C   |
| Panel Mounting        | Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. |
| Knurled Nut           | Used to attach part to panel. The max recommended torque is 10 in-lbs.                     |
| Weight (Typical)      | 2.1 oz (60g)   |
| NEMA 3R,4X, & 12      | Approved with use of ACC03.  |
| Options               | Please contact factory.  |

**Dimensions:** Inches (mm)**PART DIMENSIONS BEFORE CODE DATE: 1252 5****PART DIMENSIONS AFTER CODE DATE: 1301 1**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SC110FJ](#)