

Molded Parts Specification Control Drawing

Part Number : 222K121 thru 185-25/225

Description : Boot, 90°, With Lip

NOTES

- All dimensions are in $\frac{\text{inches}}{\text{millimeters}}$
- Dimensions appearing in table are as follows:
a - As Supplied
b - After Unrestricted Recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
- Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.
- If eyelet clip (000W212) is required with part then add CS-1858 to description (i.e. 222K121-3-0-CS-1858).




TABLE OF DIMENSIONS

PART NUMBER	H		J		P	R	S	T	U	JO	HW	JW	X	Y
	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±10%	±10%	±20%	±20%	±20%	±20%
222K121-25/225	.95 [24.0]	.41 [10.4]	.95 [24.0]	.22 [5.6]	.98 [25.0]	.98 [25.0]	.75 [19.0]	.12 [3.0]	.04 [1.0]	.33 [8.5]	.05 [1.3]	.02 [0.5]	.71 [18.0]	.63 [16.0]
222K132-25/225	1.18 [30.0]	.56 [14.2]	1.18 [30.0]	.23 [5.9]	1.26 [32.0]	1.06 [27.0]	.79 [20.0]	.12 [3.0]	.04 [1.0]	.33 [8.5]	.06 [1.5]	.03 [0.8]	.71 [18.0]	.79 [20.0]
222K142-25/225	1.22 [31.0]	.71 [18.0]	1.22 [31.0]	.28 [7.1]	1.54 [39.0]	1.22 [31.0]	.83 [21.0]	.12 [3.0]	.04 [1.0]	.59 [15.0]	.07 [1.8]	.04 [1.0]	.71 [18.0]	.79 [20.0]
222K152-25/225	1.42 [36.0]	.88 [22.4]	1.42 [36.0]	.33 [8.4]	1.81 [46.0]	1.50 [38.0]	1.02 [26.0]	.12 [3.0]	.04 [1.0]	.63 [16.0]	.07 [1.8]	.04 [1.0]	.98 [25.0]	.98 [25.0]
222K163-25/225	1.69 [43.0]	1.11 [28.2]	1.69 [43.0]	.39 [9.9]	2.17 [55.0]	1.77 [45.0]	1.18 [30.0]	.12 [3.0]	.07 [1.7]	.69 [17.5]	.08 [2.0]	.04 [1.0]	.98 [25.0]	1.18 [30.0]
222K174-25/225	2.36 [60.0]	1.38 [35.1]	2.36 [60.0]	.62 [15.7]	3.15 [80.0]	2.13 [54.0]	1.38 [35.0]	.12 [3.0]	.07 [1.7]	1.26 [32.0]	.13 [3.3]	.06 [1.5]	.98 [25.0]	1.77 [45.0]
222K185-25/225	2.60 [66.0]	1.75 [44.5]	2.60 [66.0]	.66 [16.8]	4.25 [108.0]	2.68 [68.0]	1.65 [42.0]	.12 [3.0]	.08 [2.0]	1.89 [48.0]	.15 [3.8]	.08 [2.0]	1.38 [35.0]	2.78 [70.0]



TE Connectivity
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : D1

Date : 28MAR11

Part Number : 222K121 thru 185-25/225

Description : Boot, 90°, With Lip

Molded Parts Specification Control Drawing

Part Number : 222K121 thru 185-25/225

Description : Boot, 90°, With Lip

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-25	Elastomer, Fluid Resistant	RT-1325	/225	S-1206	Adhesive

ORDERING INFORMATION			
Base part number	222K1XX	-25	-XX /225
Material dash number (See Compatibility Chart)			
Modification number (If necessary, see front of scd binder for a complete list)			
Adhesive slash number (If necessary, see Compatibility Chart)			

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE. CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION



TE Connectivity
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : D1

Date : 28MAR11

Part Number : 222K121 thru 185-25/225

Description : Boot, 90°, With Lip