



<b>DATA SHEET</b>	53015600
<b>SKINTOP BS / BSR®</b>	valid from : 27.05.2003

SKINTOP BS / BSR with polyamide spiral strain relief, is particularly used for flexible cables and handheld equipment, moving machine parts and in many applications of the instrument industry.  
Skintop BS / BSR with spiral afford protection against conductor damage.



#### The gland component parts:

gland body with lamellar design  
cap nut with spiral  
seal insert

plastic polyamide-based (UL94-V2)  
plastic polyamide-based (UL94-V2)  
elastomere

#### Technical features:

connecting thread:  
functional thread:  
IP protection:  
strain relief:  
temperature range:  
type:

Pg 7 up to Pg 21 in acc. to DIN 40 430  
multi-start trapezoidal thread  
IP 68 - 5 bar, test in acc. to DIN 40 050,  
in acc. to DIN VDE 0619  
- 20° C up to + 80° C  
BS = standard ;  
BSR = standard with reducing seal insert

#### approval :



For more information please see our current catalogue.  
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: R. Drotleff	Document: DB53015600_1EN	page 1 of 1
--------------------------------------	--------------------------	-------------