

Features:

- 1.5M Micro USB B Lead
- ErP Level 5 Efficiency Rating
- 50,000 Hour MTBF
- 1 Years Warranty




Output	
Output Voltage	+5Vdc
Minimum Load Current	0A
Nominal Load Current	2A
Nominal Output Power	10W
Output Regulation	+/-5%
Line Regulation	+/-2%
Ripple & Noise	300mVp-p Maximum
Rise Time	100mS Maximum at nominal input
Turn-on Delay	3 Seconds Maximum at nominal input
Protection	Short circuit, over current, over voltage
Efficiency	73.37%
Output Cable	1500mm Micro USB B 5 Pin

Input	
Input Voltage Range	90-264VAC
Input Frequency	47-63Hz
Input Current	0.3A Max
Inrush Current	No damage and IP fuse will not blow
AC Inlet	UK, Euro, changeable heads

Other	
Dimensions	74.1x46x36mm
Weight	Approx 150g
Operating Temp.	0 °C to 50 °C
Storage Temp.	-20 °C to +60 °C
Operating Humidity	20 ~ 85 % RH. Non-Condensing
MTBF	50,000 Hours

Diagrams



Chancerygate Business Centre, Cradock Road, Reading, Berkshire, RG2 0AH.

Tel: +44 (0) 118 931 1199 • Fax: +44 (0) 118 931 1145 • Email: info@stontronics.co.uk • Web: www.stontronics.co.uk

Please Note: Image shown is representative of entire range. Individual PSU image &/or drawings or data sheets available on request.

Stontronics Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice.