

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J3	ECR-22-153074	21SEP2022	TL	HL

NOTE:

1.MATERIAL:

HOUSING: PA9T, UL94 V-0, COLOR: (SEE TABLE).

CONTACTS: BRASS.

CAP: LCP UL94 V-0, COLOR :BLACK.

2. FINISH:

CONTACTS: 3.05um [120u"] MIN. MATTE-TIN.



1.27um [50u"] MIN. NICKEL UNDERPLATED ALL OVER.

3. WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC.

109-202, CONDITION B.



⚠ NO TE LOGO AND DATE CODE ON THE PRODUCT WITH 4 POS.

5. THE KEY IDENTIFIED WAS SHOWN ON PAGE 5.



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05 T=1.6mm

ONE BOARDLOCK
(LEFT)






REEL&CAP	BLACK PA9T	3.11	25.2	30.5	32.55	14	6-1775099-9
TRAY	IVORY PA9T	1.52	8.4	13.7	15.75	6	6-1775099-6
		5.40	46.2	51.5	53.55	24	1-1775099-3
		1.13	4.2	9.5	11.55	4	1-1775099-2
		4.30	37.8	43.1	45.15	20	1-1775099-1
		3.90	33.6	38.9	40.95	18	1-1775099-0
		3.11	25.2	30.5	32.55	14	1775099-9
		2.71	21.0	26.3	28.35	12	1775099-8
		2.31	16.8	22.1	24.15	10	1775099-7
	IVORY PA9T	1.52	8.4	13.7	15.75	6	1775099-6
		1.92	12.6	17.9	19.95	8	1775099-5
	TRANSPARENCE PA9T	5.40	46.2	51.5	53.55	24	-1775099-4
		1.13	4.2	9.5	11.55	4	-1775099-3
PACKAGE	HSG COLOR & MATERIAL	5.40	46.2	51.5	53.55	24	-1775099-2
		1.13	4.2	9.5	11.55	4	-1775099-1
		WEIGHT	DIM A	DIM B	DIM C	POS.	PART NUMBER

SUPERSEDED TO 1-1775099-3
SUPERSEDED TO 1-1775099-2
OBSOLETE


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 29JUN2022	 TE Connectivity Ltd.			
		CHK HOPE LU 29JUN2022				
		APVD HOPE LU 29JUN2022				
		PRODUCT SPEC 108-57560				
		APPLICATION SPEC				
		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT 0	A3	00779	C-1775099	—
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 8	REV J3	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—





RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05 T=1.6mm

- NOTE:
- 1.MATERIAL:
HOUSING: PA9T, UL94 V-0, COLOR: (SEE TABLE).
CONTACTS: BRASS.
 2. FINISH:
CONTACTS: 3.05um [120u"] MIN. MATTE-TIN.
1.27um [50u"] MIN. NICKEL UNDERPLATED ALL OVER.
 3. WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC.
109-202, CONDITION B.
 4. NO TE LOGO AND DATE CODE ON THE PRODUCT WITH 4 POS.
 5. THE KEY IDENTIFIED WAS SHOWN ON PAGE 5.
 6. PACKING WITH TRAY.



TWO BOARDLOCK						
IVORY PA9T	3.54	29.4	34.7	38.8	16	2-1775099-9
	5.43	46.2	51.5	55.6	24	2-1775099-8
	4.33	37.8	43.1	47.2	20	2-1775099-7
	3.93	33.6	38.9	43.0	18	2-1775099-6
	3.14	25.2	30.5	34.6	14	2-1775099-5
	2.74	21.0	26.3	30.4	12	2-1775099-4
	2.34	16.8	22.1	26.2	10	2-1775099-3
	1.95	12.6	17.9	22.0	8	2-1775099-2
	1.55	8.4	13.7	17.8	6	2-1775099-1
	1.16	4.2	9.5	13.6	4	2-1775099-0
HSG COLOR & MATERIAL	WEIGHT	DIM A	DIM B	DIM C	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 29JUN2022	 TE Connectivity Ltd.			
		CHK HOPE LU 29JUN2022				
DIMENSIONS: mm		APVD HOPE LU 29JUN2022	NAME ATX POWER CONNECTOR 4.2mm PITCH,VERTICAL ,DIP TYPE			
		PRODUCT SPEC 108-57560				
		APPLICATION SPEC				
MATERIAL		WEIGHT 0	SIZE A3	CAGE CODE 00779	DRAWING NO C-1775099	RESTRICTED TO —
		CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 8	REV J3



© 2022TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

4 POS

6 POS

8 POS

10 POS

12 POS

14 POS

16 POS

18 POS

20 POS

24 POS

KEY POSITION IDENTIFIED
(TOP VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI	29JUN2022	TE TE Connectivity Ltd.			
		CHK HOPE LU	29JUN2022				
DIMENSIONS: mm		APVD HOPE LU	29JUN2022	NAME ATX POWER CONNECTOR 4.2mm PITCH,VERTICAL ,DIP TYPE			
		PRODUCT SPEC 108-57560					
		MATERIAL —		FINISH —		APPLICATION SPEC —	
		WEIGHT 0	SIZE A3		CAGE CODE 00779	DRAWING NO C-1775099	RESTRICTED TO —
		CUSTOMER DRAWING		SCALE 1:1		SHEET 5 of 8	REV J3

1470-19 (1/15)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—


NOTES:


1. TRAY : PVC, SIZE: 330mm(L)X 265mm(W)X 22mm(H).


2. BOX : CORRUGATED, SIZE: 350mm(L)X 279mm(W)X 195mm(H).

3. QUANTITY: SEE TABLE.



5.94	4.34	80	10	800	24	2
5.93	4.33	100	10	1000	20	
5.53	3.93	100	10	1000	18	
5.85	4.25	120	10	1200	16	
6.00	4.40	140	10	1400	14	
5.98	4.38	160	10	1600	12	
5.81	4.21	180	10	1800	10	
5.89	4.29	220	10	2200	8	
5.94	4.34	280	10	2800	6	1
5.78	4.18	360	10	3600	4	
5.92	4.32	80	10	800	24	
5.90	4.30	100	10	1000	20	
6.28	4.68	120	10	1200	18	
5.95	4.35	140	10	1400	14	
5.94	4.34	160	10	1600	12	
6.22	4.62	200	10	2000	10	
6.21	4.61	240	10	2400	8	0
6.16	4.56	300	10	3000	6	
6.35	4.75	420	10	4200	4	
5.90	4.30	80	10	800	24	
5.87	4.27	100	10	1000	20	
6.24	4.64	120	10	1200	18	
5.91	4.31	140	10	1400	14	
6.42	4.82	180	10	1800	12	
6.16	4.56	200	10	2000	10	NO. OF BOARDLOCK
6.51	4.91	260	10	2600	8	
6.67	5.07	340	10	3400	6	
6.88	5.28	480	10	4800	4	
GROSS WEIGHT	NET WEIGHT	PCS /TRAY	TRAYS /BOX	PCS /BOX	POS.	




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 29JUN2022	 TE Connectivity Ltd.			
		CHK HOPE LU 29JUN2022				
DIMENSIONS: mm		APVD HOPE LU 29JUN2022	NAME			
		PRODUCT SPEC 108-57560	ATX POWER CONNECTOR 4.2mm PITCH, VERTICAL ,DIP TYPE			
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		0	A3	00779	C-1775099	—
CUSTOMER DRAWING					SCALE	SHEET
					1:1	6 of 8
					REV	J3



2. PEELING STRENGTH: 0.1 ~ 1.3 N (10 ~ 130 GRAMS)
3. PEELING SPEED: 300 mm/min.
4. EACH BAG SHALL BE INCLUDED DESICCANT.



60.4	56.4	37.0	31.28	56.0	52.4	26.2	5.7 KG	2.40 KG	140	5	700	14	6-1775099-9
W2	W1	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	GROSS WEIGHT	NET WEIGHT	PCS/ REEL	REEL/ BOX	PCS/ BOX	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 29JUN2022		TE Connectivity Ltd.											
		CHK HOPE LU 29JUN2022													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME ATX POWER CONNECTOR 4.2mm PITCH,VERTICAL ,DIP TYPE -											
															
								APVD HOPE LU 29JUN2022							
								PRODUCT SPEC 108-57560							
MATERIAL -		APPLICATION SPEC -		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
		WEIGHT 0		A3		00779		C-1775099		-					
		CUSTOMER DRAWING													
										SCALE 1:1		SHEET 7 of 8		REV J3	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

NOTES:




1. MATERIAL:

BOX: FIBREBOARD, CORRUGATED, DOUBLE WALL.
COVER TAPE: PET, TRANSPARENT COLOR.
CARRIER TAPE: POLYSTYRENES, BLACK COLOR.
REEL: POLYSTYRENES, BLUE COLOR.
BAG: POLYETHYLENE.




2. PEELING STRENGTH: 0.1 ~ 1.3 N (10 ~ 130 GRAMS)

3. PEELING SPEED: 300 mm/min.

4. EACH BAG SHALL BE INCLUDED DESICCANT.



1.95 KG	120	3	360	24	3-1775099-9
NET WEIGHT	PCS/ REEL	REEL/ BOX	PCS/ BOX	POS.	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH —
MATERIAL —	—

DWN	TONY LI	29JUN2022
CHK	HOPE LU	29JUN2022
APVD	HOPE LU	29JUN2022
PRODUCT SPEC	108-57560	
APPLICATION SPEC	—	
WEIGHT	0	

TE Connectivity Ltd.			
NAME			
ATX POWER CONNECTOR 4.2mm PITCH, VERTICAL, DIP TYPE			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1775099	—
CUSTOMER DRAWING		SCALE 1:1	SHEET 8 OF 8
		REV	J3