

D

C

B

A



Description: Stright BNC Crimp Plug For Belden 8218 Style Cable

Part No: CPMC8818

Application: For Cable Belden 8218 Style

Crimp Tool: 24-9912P

Impedance: 50 Ohms


Fequency Range: 0-4 GHz

Material:


Body	Brass	Nickel Plated
Contact	Brass	Gold Plated
Insulator	PTFE	
Crimp Sleeve	Brass	Nickel Plated
Coupling Nut	Zinc	Nickel Plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000



DIM OUTLINE



受控 CONTROLLED DOCUMENT				
编号 P/N	CPMC8818-CUST	版本 Rev	02	日期 Rel'd Date
				Aug4,11

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS		YUGE HU	07-27-11
X	± 0.5	CHECKED BY	DATE
X.X	± 0.3	YUGE HU	07-27-11
X.XX	± 0.1	APPROVED BY	DATE
ANGLES	± 0.5°	LIN MA	07-27-11
		U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

 Connectivity Solutions		
TITLE STRAIGHT BNC CRIMP PLUG FOR BLEDEN 8218 STYLE CABLE		
SHEET 1 OF 1	DRAWING NO. CPMC8818-CUST	SIZE A

DRAWING NO.

CPMC8818-CUST

REVISIONS

01	OFFICAL RELEASE					
	03-05-09	Z	B	T		
02	RELEASE FOR SUPPLIER ALTER					
	07-27-11	Y	Y	M		

CUSTOMER COPY