

## Series 800 "Mighty Mouse" Connector 800-014 Cordsets Overmolded - Environmental



**800-014**  
**Cordsets**  
**Overmolded - Environmental**

### PRODUCT FACTS

- Rugged Neoprene Jacketing
- 360° Shielding
- Straight & Right Angle Configurations
- Waterproof
- High Temperature
- Flexible Overmolded Construction

### RELATED INFORMATION

Materials and Finishes	4-5
Performance Specifications	6-9
Contact Arrangements	10
Application Tooling	A-1
Hardware and Accessories	F-1


### HOW TO ORDER

Connector Series	Connector Style End A	Connector Style End B	Class	Shell Size-Insert Arrangement	Key Position	Cable Type	Wire Gauge	Cable Exit	Overall Length
800-014	A - Plug, Hex Coupling Nut, Pin Contacts	A - Plug, Hex Coupling Nut, Pin Contacts	M - Aluminum Shell, Electroless Nickel Finish	6-4 6-7	N Normal	N - Neoprene Jacket, M22759/ 11-*-9 Primaries, Polyurethane Overmolded, No Shield	2 - #22 AWG	A - Straight Cable Exit End A and B	Overall Length in Inches (min.)
	B - Plug, Hex Coupling Nut, Socket Contacts	B - Plug, Hex Coupling Nut, Socket Contacts	NF - Aluminum Shell, Olive Drab Cadmium Over Electroless Nickel Finish	9-19 12-37	X Position X	4 - #24 AWG	B - Right Angle Exit End A and B		
	C - Receptacle, In-Line, Pin Contacts	C - Receptacle, In-Line, Pin Contacts	C - Aluminum Shell, Black Anodize Finish	14-55 15-85	Y Position Y	6 - #26 AWG	C - Straight Cable Exit End A, Right Angle Exit End B		
	D - Receptacle, In-Line, Socket Contacts	D - Receptacle, In-Line, Socket Contacts	ZN - Aluminum Shell, Zinc-Nickel Finish		Z Position Z	8 - #28 AWG	D - Right Angle Exit End A, and Straight Exit End B		
		N - No Connector Installed on End B	Z1 - Stainless Steel Shell, Passivated						
<b>Sample Part Number:</b>									
800-014	— A	A	M	6-7	N	N	4	—	72


**Series 800 "Mighty Mouse" Connector**  
**800-014 Cordsets**  
**Overmolded - Environmental**

**Glenair®**

**Series 800**  
**"Mighty**  
**Mouse"**



<b>DIMENSIONS</b>	
<b>Shell Size/ Insert Arrangements</b>	<b>A MAX</b>
6-4, 6-7	1.200 (30.5)
9-19	1.400 (35.6)
12-37	1.500 (38.1)
14-55	1.650 (41.5)
15-85	1.750 (44.5)



Metric Dimensions (mm) are in parentheses.

## Tired of waiting an eternity for a simple connector or accessory?



### Then Glenair's "Same Day Delivery" program is the answer.

Tired of long lead times for connectors and accessories? Then consider over 30,000 different part numbers in stock, in quantity, and ready for immediate shipment - including virtually every Mil Spec accessory in the book. Consider as well


Glenair's "no minimum order" policy and our lightning fast turnaround on quotes for price and delivery. At Glenair, we're making unprecedented investments in inventory to keep current with your every need.



Commercial and Mil Spec connector accessories



Convoluted tubing and metal-core conduit




Electrical and fiber optic cable assemblies



Composite thermoplastic components



Microminiature connectors and accessories



Backshell assembly and termination tools



1211 Air Way  
Glendale, California 91201-2497

Telephone: 818-247-6000 · Facsimile: 818-500-9912 · Email: [sales@glenair.com](mailto:sales@glenair.com)

United States · United Kingdom · Germany · Nordic · France · Italy

[www.glenair.com](http://www.glenair.com)