






Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 50mA/12VDC
- Contact resistance: 100mΩ max.
- Insulation resistance: 100MΩ min. @ 500VDC
- Dielectric strength: 250VAC for 1 minute
- Life: 500,000 cycles

Mechanical Specifications:

- Type: SPST
- Operation force: 160±50gf
- Stroke: .35mm +.2mm -.1mm
- Operating temperature: -25°~70°C

Material:

- Button color: brown

Note:

- RoHS Compliant and are also process compatible with 260° solder

Tactile Switch (Thru-Hole)
101-0121-EV

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0121-EV](#)