



T-01-01

Diode Data

Diode Data

Computer Diodes (Glass Package)

Device No.	Package No.	V _{RRM} V Min	I _R nA Max	@ V _R V	V _F V Min	@ V _F Max	I _F mA	C pF Max	t _{rr} ns Max	Test Cond.	Proc. No.	
1N625	DO-35	30	1000	20		1.5	4		1000	(Note 1)	D4	
1N914	DO-35	100	25 5000	20 75		1.0	10		4	(Note 2)	D4	
1N914A	DO-35	100	25 5000	20 75		1.0	20		4	(Note 2)	D4	
1N914B	DO-35	100	25 5000	20 75		0.72 1.0	5 100		4	(Note 2)	D4	
1N916	DO-35	100	25 5000	20 75		1.0	10		4	(Note 2)	D4	
1N916A	DO-35	100	25 5000	20 75		1.0	20		4	(Note 2)	D4	
1N916B	DO-35	100	25 5000	20 75		0.73 1.0	5 30		4	(Note 2)	D4	
1N3064	DO-35	75	100	50		0.575 0.650 0.710 1.0	0.250 1.0 2.0 10.0	2	4	(Note 3)	D4	
1N3600	DO-35	75	100	50		0.54 0.66 0.76 0.82 0.87	0.62 0.74 0.86 0.92 1.0	1.0 10.0 50.0 100.0 200.0	2.5	4	(Note 4)	D4
1N4009	DO-35	35	100	25		1.0	30	4	2	(Note 2)	D4	
1N4146	DO-35	See Data for 1N914A/914B										
1N4147	DO-35	See Data for 1N914A/914B										
1N4148	DO-35	See Data for 1N914										
1N4149	DO-35	See Data for 1N916										
1N4150	DO-35	See Data for 1N3600										
1N4151	DO-35	75	50	50		1.0	50	4	2	(Note 2)	D4	
1N4152	DO-35	40	50	30		0.49 0.53 0.59 0.62 0.70 0.74	0.55 0.59 0.67 0.70 0.81 0.88	0.1 0.25 1.0 2.0 10.0 20.0	4	2	(Note 2)	D4
1N4153	DO-35	75	50	50	See 1N4152			4	2	(Note 2)	D4	
1N4154	DO-35	35	100	25		1.0	30	4	2	(Note 2)	D4	

2