




- 1

BULK PACKAGED 50 PER UNIT.
- 2

PACKAGE MUST BE MARKED "KANNEGIETER CODE CGV 0103"
- 3

MATERIAL

a) BODY: BRASS

b) FERRULE: STAINLESS STEEL

c) NUT: BRASS

d) CRIMP SLEEVE: BRASS

e) DUST CAP: VINYL, COLOR, RED

f) HALF & FULL SLEEVE: DELRIN, COLOR, WHITE
- 4

MATERIAL

a) BODY: STAINLESS STEEL

b) FERRULE: STAINLESS STEEL

c) NUT: BRASS

d) CRIMP SLEEVE: BRASS

e) DUST CAP: VINYL, COLOR, RED

f) HALF & FULL SLEEVE: DELRIN, COLOR, WHITE
- 5

FINISH

a) BODY, NUT, CRIMP SLEEVE: NICKEL PLATE
- 6

FINISH

a) NUT, CRIMP SLEEVE: NICKEL PLATE
- 7

3.1mm STRAIN RELIEF: THERMOPLASTIC ELASTOMER, CLR, BLACK
- 8

4.1mm STRAIN RELIEF: VINYL, COLOR, BLACK
- 9

5.3mm HEAT SHRINK TUBING: POLYOLEFIN, COLOR, BLACK

OBSOLETE	68.86 [2.711]	7	436µm	3.1mm MAX	5	3	2-504014-5
OBSOLETE	68.86 [2.711]	7	229µm	3.1mm MAX	6	4	2-504014-4
OBSOLETE	66.72 [2.627]	8	140µm	4.3mm MAX	5	3	2-504014-3
OBSOLETE	68.86 [2.711]	7	240µm	3.1mm MAX	5	3	2-504024-1
OBSOLETE	68.86 [2.711]	7	600µm	3.1mm MAX	5	3	2-504014-0
OBSOLETE	53.04 [2.088]	9	240µm	5.3mm MAX	5	3	1-504014-9
OBSOLETE	68.86 [2.711]	7	140µm	3.1mm MAX	6	4	1-504014-4
OBSOLETE	53.04 [2.088]	9	140µm	5.3mm MAX	5	3	1-504014-2
OBSOLETE	66.72 [2.627]	8	140µm	4.3mm MAX	5	3	1-504014-1
	68.86 [2.711]	7	140µm	3.1mm MAX	5	3	1-504014-0
OBSOLETE	66.72 [2.627]	8	125µm	4.3mm MAX	6	4	504014-6
	68.86 [2.711]	7	125µm	3.1mm MAX	6	4	504014-5
OBSOLETE	53.04 [2.088]	9	125µm	5.3mm MAX	5	3	504014-4
OBSOLETE	53.04 [2.088]	9	125µm	5.3mm MAX	5	3	504014-3
OBSOLETE	66.72 [2.627]	8	125µm	4.3mm MAX	5	3	504014-2
OBSOLETE	68.86 [2.711]	7	125µm	3.1mm MAX	5	3	504014-1
A MAX		BOOT	HOLE SIZE	CABLE SIZE	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.HILEMAN 9-3-92	AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK P.YEAGER 9-28-02		
DIMENSIONS: mm [INCHES]		APVD S.BUCHTER 9-28-02	NAME	
		PRODUCT SPEC	906 CONNECTOR KIT	
		APPLICATION SPEC		
MATERIAL SEE TABLE		WEIGHT -	SIZE A2	CAGE CODE 00779
FINISH SEE TABLE		CUSTOMER DRAWING	DRAWING NO C-504014	RESTRICTED TO -
SCALE NT5			SHEET 1	REV K

