






Issue No.	Eng. Ref. No.	REVISIONS	Date	App. By
1	—	ORIGINAL	17/03/09	paramesh
3	1232	ØA DIMENSION CHANGED	16/04/09	paramesh

BAND LOCK BACKSHELL :-



STYLE-2 : MODIFICATION


PART NUMBERING SYSTEM :-



Amphenol

AIPL

TITLE
BAND LOCK ADAPTER (BK4)
FOR CONNECTORS MIL-C-38999 SERIES III & IV



All Dimensions are in
INCHES(MM)

STANDARD

Dwg. No.
Size
A4

Dwg.No.

PSTDBS237

Doc. No.: QF-DEV-76
REV. NO. : 02

Sheet 1 OF 2

Name	Date
Drawn by <i>Panthosh</i>	16/03/09
Checked by <i>Vinod</i>	17/03/09
App.by <i>paramesh</i>	17/03/09

Issue No.	Eng. Ref. No.	REVISIONS	Date	App. By
1	—	ORIGINAL	17/03/09	<i>paramesh</i>
3	1232	ØA DIMENSION CHANGED	16/04/09	<i>paramesh</i>

👉 DIMENSIONS :-

SHELL SIZE DESIGNATOR	MAX. ENTRY SIZE	CONNECTOR SHELL SIZE/CODE	ØA MAX.		ØM THREADS	D MAX.		E MAX.		G MAX.		F MAX.	
			INCH	MM		INCH	MM	INCH	MM	INCH	MM	INCH	MM
08	04	09/A	0.75	19.10	M12X1.0	0.52	13.20	1.15	29.21	1.28	32.51	0.84	21.33
10	06	11/B	0.85	21.60	M15X1.0	0.54	13.72	1.17	29.72	1.34	34.03	0.97	24.64
12	08	13/C	1.00	25.40	M18X1.0	0.57	14.48	1.20	30.50	1.41	35.81	1.09	27.69
14	10	15/D	1.15	29.20	M22X1.0	0.59	14.99	1.23	31.25	1.47	37.33	1.22	30.98
16	12	17/E	1.25	31.80	M25X1.0	0.62	15.75	1.25	31.75	1.53	38.86	1.34	34.03
18	13	19/F	1.40	35.60	M28X1.0	0.63	16.00	1.26	32.00	1.59	40.38	1.41	35.81
20	15	21/G	1.50	38.10	M31X1.0	0.66	16.76	1.29	32.76	1.66	42.16	1.53	38.86
22	17	23/H	1.65	41.90	M34X1.0	0.68	17.30	1.32	33.53	1.72	43.68	1.66	42.16
24	19	25/J	1.75	44.50	M37X1.0	0.71	18.00	1.34	34.03	1.78	45.21	1.78	45.21

👉 ENTRY SIZE DIMENSIONS :-


ENTRY SIZE	ØB +0.010-0.020 (+0.25-0.50)		ØC ±0.015 (±0.381)		ØH MAX	
	INCH	MM	INCH	MM	INCH	MM
02	0.125	3.17	0.209	5.30	N/A	N/A
03	0.188	4.75	0.271	6.88	N/A	N/A
04	0.250	6.35	0.334	8.48	N/A	N/A
05	0.312	7.92	0.396	10.05	0.734	18.64
06	0.375	9.52	0.459	11.65	0.734	18.64
07	0.438	11.12	0.521	13.23	0.858	21.79
08	0.500	12.70	0.584	14.83	0.858	21.79
09	0.562	14.30	0.646	16.40	N/A	N/A
10	0.625	15.88	0.709	18.00	1.112	28.24
11	0.688	17.50	0.768	19.50	1.112	28.24
12	0.750	19.05	0.834	21.18	1.345	34.16
13	0.812	20.65	0.894	22.70	1.345	34.16
14	0.875	22.23	0.959	24.35	1.345	34.16
15	0.938	23.83	1.020	25.90	1.345	34.16
16	1.000	25.40	1.084	27.53	1.594	40.48
18	1.125	28.58	1.209	30.70	1.594	40.48
20	1.250	31.75	1.334	33.88	1.969	50.01
22	1.375	34.92	1.459	37.05	2.219	56.36
24	1.500	38.10	1.584	40.23	2.219	56.36

👉 MATERIAL :-

- ↗ Aluminium alloy as per ASTM B211 / B85
- ↗ Corrosion resistant steel as per AMS-QQ-S-763

👉 NOTE:

- ↗ When Maximum Cable Entry Exceed's Connector Shell Diameter, Style-2 will be Supplied.

Amphenol AIPL			TITLE BAND LOCK ADAPTER (BK4) FOR CONNECTORS MIL-C-38999 SERIES III & IV				
						All Dimensions are in INCHES(MM)	
	Name	Date	Dwg. Size A4	Dwg.No. PSTDBS237		STANDARD	
Drawn by	<i>Panthosh</i>	16/03/09		Doc. No.: QF-DEV-76 REV. NO. : 02			
Checked by	<i>Vinod</i>	17/03/09					
App.by	<i>paramesh</i>	17/03/09					
				Sheet 2 OF 2			