


Dry Lining Boxes

PRO-ELEC



Construction:

Description	Material
Base	ABS

Standard:

BS 5733.

Conditions of Use:

- a) An ambient temperature in the range -5°C to +40°C, the average value over 24 hours not exceeding 25°C.
- b) A situation not subject to exposure to direct radiation from the sun or other source of heat like to raise temperatures above the limits.
- c) An altitude not exceeding 2000 metres above sea level; an atmosphere no subject to abnormal pollution by smoke, chemical fumes, rain, spray, prolonged periods of high humidity or other abnormal conditions.

Safety Specifications:

Item	Conditions	Requirements
Appearance	-	No defect such as cracks, deep scratches or blemishes.
Marking	-	Shall be legible and must be clear.
Insulation resistance	500 + 250V dc for 1 minute.	Shall not be less than 5MΩ.
Dielectric strength	2000 ±60V for 1 minute.	No damage or breakdown.
Resistance to aging	70° ±5° (168 hours).	No cracks or become sticky.
Construction	20° ±5°.	Complied with Figure 9 and 21 gauge.
Torque test	Value of 0.6Nm (6.1kgf/cm).	Terminal, cord grip and cover screws shall withstand the torque applied.
Glow wire test	650°/850° electrically heated.	Flame must extinguish within 30 seconds.
Temperature rise	14A, 250V.	Temperature rise must not exceed: 1. Terminals or terminations : 52K. 2. Accessible surface : 52K.
Make and break test of switch	13A, 250V (15,000 times)	Voltage drop across each switched pole shall not exceed 75mV.
Cord anchorage test	1. 3kg. Pull force test for 0.5mm ² cable. 2. 6kg. Pull force test for 1.0 mm ² or above cable.	The flexible cord shall not be displaced by more than 2mm after being pull 25 times.

PRO-ELEC

Dry Lining Boxes



Specification Table

Description	Type	Part Number
Back Box, Dry Lining, Single, 47mm	1 Gang Pattress Box	858-47
Back Box, Dry Lining, Double, 47mm	2 Gang Pattress Box	8588-47



Dry Lining Boxes

PRO-ELEC

Notes:

International Sales Offices:



AUSTRALIA – Farnell

Tel No: ++61 1300 361 005
Fax No: ++61 1300 361 225



FINLAND – Farnell

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



ITALY – Farnell

Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell

Tel No: 901 20 20 80
Fax No: 901 20 20 90



AUSTRIA – Farnell

Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell

Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



MALAYSIA – Farnell-Newark

Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell

Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62



BELGIUM – Farnell

Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell

Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NETHERLANDS – Farnell

Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell

Tel No: ++ 44 204 64 64
Fax No: ++ 44 204 64 54



BRAZIL – Farnell-Newark

Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark

Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



NEW ZEALAND – Farnell

Tel No: 0800 90 80 80
Fax No: 0800 90 80 81



UK – Farnell

Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



CHINA – Farnell-Newark

Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



HUNGARY - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



NORWAY – Farnell

Tel No: 800 146 70
Fax No: 800 146 76



UK – CPC

++ 44 8701 202 530
++ 44 8701 202 531



CZECH REPUBLIC - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



INDIA - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



PORTUGAL – Farnell

Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



USA – Newark

Tel No: 800 463 9275



DENMARK – Farnell

Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



IRELAND – Farnell

Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



RUSSIA – Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



EXPORT – Farnell

Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



ESTONIA – Farnell

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



ISRAEL – Farnell

Tel No: ++ 180 937 0015
Fax No: ++ 180 937 0014



SINGAPORE – Farnell-Newark

Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300

<http://www.farnell.com>

<http://www.newark.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-Elec is the registered trademark of the Group. © Premier Farnell plc 2009.

PRO-ELEC