

5/8-24UNEF-2B




5/8-24UNEF-2A

13.45 ON FLATS

3.00 [.118]

22.00 [.867]

45.60 [1.797]



1. MAX. PANEL THICKNESS = 6.5mm

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
8					DRAWN	G.R.S.	09/23/07								
7					CHECKED			PART DESCRIPTION N PLUG TO N BULKHEAD JACK ADAPTER							
6	HEX NUT	BRASS	NEXCOTE		1	ISSUED									
5	LOCK WASHER	BRASS	NEXCOTE		1	SHEET	1					OF	1	PART NO. 172336	
4	GASKET	SILICONE	RED		1										
3	CONTACT PIN	PHOS. BRONZE	GOLD		1	CAD FILE			DWG. NO. 172336.DWG						
2	INSULATOR	TEFLON	NATURAL		1	C:/172/172336.DWG							REV.	NC	SIZE
1	BODY	BRASS	NEXCOTE	1											
				DESCRIPTION		MATERIAL		FINISH		QTY					