


1

2

3

4



REMARK:

1. MATERIALS:

CONTACTS: COPPER ALLOY T=0.20mm, GOLD(G\F or 30u") TOP OVER CONTACT AREA, 50u" Min. NICKEL UNDER PLATE.

2. PART NUMBER DESCRIPTION: 10090933-S XX X X LF

SERIES NO. _____
TYPE _____
S: SOCKET (FEMALE)
GAUGE SIZE _____
24: 24-28(AWG)
CONTACT FINISH _____
4: GOLD FLASH
6: 30u" GOLD
LF: ROHS COMPLIANT
PACKAGING _____
8: BOX, 500 PCS
9: REEL, 10K PCS

SIZE	PART NO.	PACKAGING
24-28AWG	10090933-S24*8LF	BOX, 500PCS
24-28AWG	10090933-S24*9LF	REEL, 10KPCS

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	.X ± 0.38	.XX ± 0.25	projection	title	www.fciconnect.com	
A	T09-1157	J.H	12/10/09	linear	.XX ± 0.25	.XXX ± 0.10	MM	H/D D-SUB CRIMPING FEMALE CONTACT		
B	T10-0164	J.H	10/19/10	angles	0° ± 2°		1:1	product family D-SUB		
				dr	JASON HSU	10/19/10		size		
				enrg	JASON HSU	10/19/10		dwg no		
				chr	GARY HSIEH	10/19/10		code		
				appd	JOSEPH HSIA	10/19/10		sheet		
sheet index	revision	B								
	sheet	1								

cage code

ACAD

PDM: Rev:B

STATUS: Released

Printed: Nov 02, 2010