

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]				
	ENGLISH	METRIC	L ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
PM1-3F*	--	M3	.63 [16,00]	.23 [5,84]	.22 [5,59]	.49 [12,45]	.13 [3,30]
P18-6F	#6	M3,5	.63 [16,00]	.30 [7,62]	.21 [5,33]	.49 [12,45]	.15 [3,81]
P18-6FN*	#6	M3,5	.63 [16,00]	.24 [6,10]	.19 [4,83]	.49 [12,45]	.15 [3,81]
P18-8F	#8	M4	.69 [17,53]	.32 [8,13]	.25 [6,35]	.53 [13,46]	.17 [4,32]
P18-10F	#10	--	.71 [18,03]	.35 [8,89]	.25 [6,35]	.55 [13,97]	.20 [5,08]
P18-10FN*	#10	--	.71 [18,03]	.31 [7,87]	.25 [6,35]	.55 [13,97]	.20 [5,08]
PM1-5F*	--	M5	.71 [18,03]	.35 [8,80]	.26 [6,60]	.55 [13,97]	.20 [5,08]
P18-14F	1/4"	M6	.88 [22,35]	.44 [11,18]	.33 [8,38]	.63 [16,00]	.27 [6,86]

*NOT CSA CERTIFIED

NOTES:

- UL LISTED & CSA CERTIFIED FOR:
 - #22-16 AWG [0,5-1,5 mm²] SOLID OR STRANDED COPPER WIRE
 - 302°F [150°C] MAX. OPERATING TEMPERATURE
 - 2000 VOLTS MAX


- SEE www.panduit.com FOR PACKAGE QUANTITIES


- MATERIAL:
 - STAMPING: .032" [0,8] THK COPPER, TIN PLATED

- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT

- WIRE STRIP LENGTH: 9/32" ^{+1/32}₋₀ [7,1mm ^{+0,8}₋₀]

UL & CSA TOOLS
CT-100A CT-200 CT-600-A (CT-570CH) CT-1570 CT-2500 (CT-2570CH)
PANDUIT APPROVED TOOLS
CT-160 CT-260



TITLE				
#22-16 BARREL NON-INSULATED FORK				
CUSTOMER DRAWING				
ITEM REVISION NAME				
N41461BA/10				
DATASET FILE NAME			MATERIAL: SEE NOTES DRAWING NUMBER: A41461	
N41461BA_DC/10				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				
.X ± .XX ± .XXX ± ANGLES ±				
			THIRD ANGLE PROJECTION	
DRAWN BY		DATE		
DRL		-		
CHK		SCALE	SHEET 1 OF 1 A	
		N.T.S.		