


## Paper Labels (B-424)

Economical choice for light duty general ID.

- White finish and matte topcoat
- Excellent contrast and smear resistance for bar code printing

Service temp: -40°F to 124°F  
Agency approvals: **RoHS**




| Fits Printer Model(s) | Diagram | Catalog #  | Color | Label Width A Inch (mm) | Label Height B Inch (mm) | Horiz. Repeat C Inch (mm) | Vert. Repeat D Inch (mm) | Web Width E Inch (mm) | Labels Per Row | Labels Per Roll | Rec. Ribbon |
|-----------------------|---------|------------|-------|-------------------------|--------------------------|---------------------------|--------------------------|-----------------------|----------------|-----------------|-------------|
| BBP33 only            | Fig. 2  | B33-17-424 | White | 2.000 (50.8)            | 1.000 (25.4)             |                           | 1.125 (28.6)             | 2.200 (55.9)          | 1              | 1500            | B30-R4300   |
| BBP33 only            | Fig. 2  | B33-18-424 | White | 3.000 (76.2)            | 1.000 (25.4)             |                           | 1.125 (28.6)             | 3.200 (81.3)          | 1              | 1500            | B30-R4300   |
| BBP33 only            | Fig. 2  | B33-19-424 | White | 3.000 (76.2)            | 2.000 (50.8)             |                           | 2.125 (54.0)             | 3.200 (81.3)          | 1              | 500             | B30-R4300   |
| BBP33 only            | Fig. 2  | B33-25-424 | White | 4.000 (101.6)           | 6.000 (152.4)            |                           | 6.125 (155.6)            | 4.200 (106.7)         | 1              | 350             | B30-R4300   |

## Polypropylene Labels (B-425)

General labeling material for indoor use.

- Outstanding chemical and solvent resistance and print performance
- Not recommended for prolonged outdoor use (use B-595 material on p.14 for 8-10 year outdoor use)

Service temp: -94°F to 212°F  
Agency approvals: **UL** **UL** **RoHS** **CE**




| Fits Printer Model(s) | Diagram | Catalog #  | Color | Label Width A Inch (mm) | Label Height B Inch (mm) | Horiz. Repeat C Inch (mm) | Vert. Repeat D Inch (mm) | Web Width E Inch (mm) | Labels Per Row | Labels Per Roll | Rec. Ribbon |
|-----------------------|---------|------------|-------|-------------------------|--------------------------|---------------------------|--------------------------|-----------------------|----------------|-----------------|-------------|
| BBP33 only            | Fig. 1  | B33-5-425  | White | 1.000 (25.4)            | 0.500 (12.7)             | 1.075 (27.3)              | 0.600 (15.2)             | 3.350 (85.1)          | 3              | 5000            | B30-R4300   |
| BBP33 only            | Fig. 2  | B33-17-425 | White | 2.000 (50.8)            | 1.000 (25.4)             |                           | 1.125 (28.6)             | 2.200 (55.9)          | 1              | 1500            | B30-R4300   |
| BBP33 only            | Fig. 2  | B33-18-425 | White | 3.000 (76.2)            | 1.000 (25.4)             |                           | 1.125 (28.6)             | 3.200 (81.3)          | 1              | 1500            | B30-R4300   |
| BBP33 only            | Fig. 2  | B33-19-425 | White | 3.000 (76.2)            | 2.000 (50.8)             |                           | 2.125 (54.0)             | 3.200 (81.3)          | 1              | 500             | B30-R4300   |

## Outdoor Grade Vinyl Labels (B-595)

For 8-10 year outdoor use.

- Semi-gloss topcoat
- Good chemical, moisture, UV and weather resistance
- Highly pliable material conforms to rough and curved surfaces and equipment
- Average outdoor durability of the label is 8-10 years, depending on placement

Service temp: -40°F to 180°F  
Application temp: 0°F to 180°F



| Fits Printer Model(s) | Diagram | Catalog #          | Color  | Label Width A Inch (mm) | Label Height B Inch (mm) | Horiz. Repeat C Inch (mm) | Vert. Repeat D Inch (mm) | Web Width E Inch (mm) | Labels Per Row | Labels Per Roll | Rec. Ribbon |
|-----------------------|---------|--------------------|--------|-------------------------|--------------------------|---------------------------|--------------------------|-----------------------|----------------|-----------------|-------------|
| BBP31, BBP33          | Fig. 2  | B30-242-595-BLNKWT | White  | 2.850 (72.4)            | 1.125 (28.6)             |                           | 3.250 (82.6)             | 1.375 (35.0)          | 1              | 300             | B30-R10000  |
| BBP31, BBP33          | Fig. 2  | B30-241-595-BLNKWT | White  | 3.000 (76.2)            | 2.250 (57.2)             |                           | 3.250 (82.6)             | 2.500 (63.5)          | 1              | 300             | B30-R10000  |
| BBP31, BBP33          | Fig. 2  | B30-241-595-BLNKYL | Yellow | 3.000 (76.2)            | 2.250 (57.2)             |                           | 3.250 (82.6)             | 2.500 (63.5)          | 1              | 300             | B30-R10000  |
| BBP31, BBP33          | Fig. 2  | B30-219-595-BLNKWT | White  | 3.850 (97.8)            | 2.250 (57.2)             |                           | 4.250 (108.0)            | 2.500 (63.5)          | 1              | 250             | B30-R10000  |
| BBP31, BBP33          | Fig. 2  | B30-25-595-BLNKWT  | White  | 6.000 (152.4)           | 4.000 (100.0)            |                           | 6.250 (158.8)            | 4.250 (108.0)         | 1              | 175             | B30-R10000  |
| BBP31, BBP33          | Fig. 2  | B30-25-595-BLNKYL  | Yellow | 6.000 (152.4)           | 4.000 (100.0)            |                           | 6.250 (158.8)            | 4.250 (108.0)         | 1              | 175             | B30-R10000  |