



General ordering data

Order No.	1697460000
Part designation	SKMU PG11-K GR
Version	Locknut, Polyamide 6, External thread: PG 11
EAN	4008190880576
Qty.	100 pc(s).

General details

AF size 1	24 mm
Assembly temperature, max.	100 °C
Assembly temperature, min.	-30 °C
External thread	PG 11
Internal thread	PG 11
Length of thread	5 mm
Material	Polyamide 6
RAL colour	RAL 7035
Thickness	5 mm
Type of cable gland	PG

Approvals

Approvals institutes	n.a.
----------------------	------

Classifications

ETIM 2.0	EC000940
ETIM 3.0	EC000940
eClass 4.1	23-11-07-01
eClass 5.0	23-11-07-01
eClass 5.1	23-11-07-01

Similar products

Order No.	Part designation	Version
1772440000	SKMU M12 - K GR	Locknut, Polyamide 6, External thread: M 12 x 1.5

1772450000	SKMU M16 - K GR	Locknut, Polyamide 6, External thread: M 16 x 1.5
1772460000	SKMU M20 - K GR	Locknut, Polyamide 6, External thread: M 20 x 1.5
1772470000	SKMU M25 - K GR	Locknut, Polyamide 6, External thread: M 25 x 1.5
1772480000	SKMU M32 - K GR	Locknut, Polyamide 6, External thread: M 32 x 1.5
1772490000	SKMU M40 - K GR	Locknut, Polyamide 6, External thread: M 40 x 1.5
1772500000	SKMU M50 - K GR	Locknut, Polyamide 6, External thread: M 50 x 1.5
1772510000	SKMU M63 - K GR	Locknut, Polyamide 6, External thread: M 63 x 1.5
1697470000	SKMU PG 13,5-K GR	Locknut, Polyamide 6, External thread: PG 13.5
1697480000	SKMU PG16-K GR	Locknut, Polyamide 6, External thread: PG 16
1698220000	SKMU PG21-K GR	Locknut, Polyamide 6, External thread: PG 21
1698230000	SKMU PG29-K GR	Locknut, Polyamide 6, External thread: PG 29
1698240000	SKMU PG36-K GR	Locknut, Polyamide 6, External thread: PG 36
1698250000	SKMU PG42-K GR	Locknut, Polyamide 6, External thread: PG 42
1719090000	SKMU PG48-K GR	Locknut, Polyamide 6, External thread: PG 48
1697440000	SKMU PG7-K GR	Locknut, Polyamide 6, External thread: PG 7
1697450000	SKMU PG9-K GR	Locknut, Polyamide 6, External thread: PG 9