




- Material and Finish:
1. Insulator Material: Nylon 66, UL94V-0, Color: White
 2. Contact Material: Brass
 3. Contact Plated: Tin Plated
 4. Current Rating: 7A AC/DC
 5. Voltage Rating: 250V AC Maximum
 6. Contact Resistance: 20 mohm Max.
 7. Insulation Resistance: 1000 Mohm Min.
 8. Dielectric Withstanding Voltage: 1500V AC/minute
 9. Operating Temperature: -25°C to +85°C
 10. RO = RoHS

PART NO.	TITLE	A	B	C
13500100	PMT-02ST-RO	3.96	7.92	5.52
13500110	PMT-05ST-RO	15.84	19.80	17.4
13500140	PMT-03ST-RO	7.92	11.88	9.48
13500150	PMT-04ST-RO	11.88	15.84	13.44
13500130	PMT-06ST-RO	19.80	23.76	21.36



UNLESS OTHERWISE SPECIFIED TOLERANCE		天衛電子股份有限公司 David Electronics Co., Ltd. TEL: 886-2-8647-1376 FAX: 886-2-8647-1377	
ANG.	±	大欣電子五金廠(深圳) Daxin Electronic & Metal Factory TEL: 86 755-2768 2800 FAX: 86 755-2708 2505	
0	±0.25	APPLICATION NO.: ECN-0604167, ECN-0804171	
.00	±0.15	DRAWN NAME: PMT-XXST-RO	
.000	±0.05	PRODUCT NO.: 1350XXXX	
SCALE: NONE	UNIT: mm	FILE NAME: 2-612	
DRAWN: 6/14/06	CHECKED: 6/14/06	APPROVED: 6/14/06	
DATE: 06/14/06	DATE: 04/26/06	DATE: 06/14/06	

REV.	DESCRIPTION	DATE	REV.	DESCRIPTION	DATE
1	ECN-0606071	06/14/06			
2	ECN-0604167, ECN-0604171	04/26/06			