




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART#	DESCRIPTION	WEIGHT*
CJE688TG**	8 POSITION, 8 WIRE UNIVERSAL MODULE. WHITE WIRE CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.73 LB/100 PCS (785g/100 PCS)

*WEIGHT IS APPROXIMATE
**JACK COLOR SUFFIX

NOTES:

1. JACK MODULE USES SEALANT(S) TO PROTECT CONTACTS FROM CORROSION AND CONTAMINATION.
2. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
3. TO DESIGNATE A JACK COLOR, ADD A TWO LETTER COLOR SUFFIX. SEE CURRENT CATALOG FOR AVAILABLE PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
4. MATERIAL:
MODULE HOUSING - PBT
WIRE CAP - PC
STRAIN RELIEF CLIP - PC
5. ALL TX6 CAT6 8 POSITION, 8 WIRE CONNECTOR MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
6. DIMENSIONS IN PARENTHESES ARE IN METRIC.



MODEL FILENAME		M02115AA/00	SIZE A
DRAWING FILENAME		10M168BB_DC02/00B	
TX6 PLUS CORROSIVE RESISTANT JACK MODULE CUSTOMER DRAWING			
 TINLEY PARK, IL 60487		I.I. NUMBER	
		PRODUCT SPEC/ PKG SPEC	
 THIRD ANGLE PROJECTION		ASSY METHOD/ TEST METHOD	
		SCALE FULL	
DRAWN BY BJN		PART NO. CJE688TG**	
DATE 2-23-10		DRAWING NO. 10M168BB-02	
CHK'D KAA		MAT'L	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	6-4-10	BJN	KAA	B. UPDATED TITLE BLOCK A. UPDATED WEIGHT	10M168BB-02		PBD		
R	2-23-10	BJN	KAA	RELEASED TO PRODUCTION	10M168BB-02		PBD		