



Work And Tool Holding

Plain Clamps



Material
Heat-treated steel, enamelled.
DIN 6314

489236

B1 (mm)	F (mm)	Bolt Size (mm)	A (in)	B2 (mm)	B3 (mm)	E1 (mm)	E2 (mm)	Order Code	Price Each
9	60	M8	5/16	12	25	10	13	22	137-8319
11	80	M10	3/8	15	30	12	15	30	137-8318
14	125	M12	1/2	20	40	14	21	50	137-8317
18	125	M14							
		M16	5/8	25	50	16	26	45	137-8316
		M18							
22	160	M20	3/4	30	60	22	30	60	137-8315
		M22							