

Ferrule - A 0,25- 5 - 3202465

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ferrule, Length: 5 mm, Color: silver

The figure shows variant A 1-6

Product Features

- ✓ The A 0,25.. ferrules can also be used to process 0.14 mm² conductors
- ✓ The dimensions of the ferrules conform to DIN 46228-1
- ✓ The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

Key commercial data

Packing unit	1 1
Minimum order quantity	1000 1
Weight per Piece (excluding packing)	0.02 GRM
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Length (b)	5 mm
Sleeve length	4.3 mm
Inner dimension of the insulating collar (d)	1.7 mm
Ferrule diameter	0.8 mm
Sleeve wall thickness	0.15 mm

Ambient conditions

Max. permanent temperature	105 °C
----------------------------	--------

General

Color	silver
Material	E-CU

Ferrule - A 0,25- 5 - 3202465

Classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400201

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

Approvals

Approvals

Approvals

CSA / CSAus / cCSAus

Ex Approvals

Approvals submitted

Approval details

Ferrule - A 0,25- 5 - 3202465

Approvals



CSAus

cCSAus