





PANEL THICKNESS	X dimension
0.75-1.25 [0.30-.049]	19.2 -0.1 [7.56]
1.25-2.0 [0.49-.079]	19.4 -0.1 [7.64]
2.0-3.0 [0.79-1.18]	19.8 -0.1 [7.80]



PANEL CUTOOUT
NOT TO SCALE




SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
DN	NONE	DN
1a-1	OPEN	1-1b



CIRCUIT: SPD

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR
6A @ 250VAC
5. MATERIALS: TERMINALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: <20 Mega Ω
8. INSULATION RESISTANCE: >1000 Mega Ω
9. DIELECTRIC STRENGTH: >1500 V 1 minute
>3000 V between poles



				TITLE
A	11663	RELEASED FOR PRODUCTION	9/18/01	CJB
REV.	ECN NO.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
TITLE				
R1966C BLK BLK EF				
SCALE	DATE	DR	DWG	REV
1.5:1	9/18/01	CJB	M302200	A