


Advantages of Using Clips

- **Metal hold-down clips** are ideal for use where high heat or humid conditions are a factor, thus holding their shape and tension. The clips are made of stainless steel and are designed to withstand harsh environments.
- **Plastic ejector/hold-down clips** are ideal in applications where sockets are located in dense or tight areas. These clips allow for quick, safe and firm securing of relays in the sockets with the added benefit that the relay can be ejected with one finger. Plastic clips also aid in keeping operator's fingers away from live circuits. The optional snap-in identification tag allows for custom marking of sockets when used in multi-socket applications.
- **Plastic I.D. clips** are ideal for easy identification of circuits in multi-relay applications. They are designed for labeling and are not ideal for securing the relay in the socket.


Plastic Ejector Clip




Metal Hold-Down Clip



Plastic I.D. Clip




Metal and Plastic Clips



- Stainless Steel Clips are Designed to be Corrosion Resistant in Harsh Environments and are Ideal for Use Under Shock and Vibration Conditions.

- Plastic Ejector/Hold-Down Clips are Ideal for Use in High-Density, Multi-Socket Applications.



- Plastic Identification Tag is Perfect for Use in Multi-Socket Applications for Custom Identification of Circuits.



16-781SC



16-781IDC



16-782SC



16-782PC-1



16-782IDC



16-783SC




16-783IDC



16-784SC



16-784IDC




16-1332




16-1324



16-1342



16-1351



16-1344



16-TDR782SC



16-TDRPROSC

Socket Part Number	Clip Part Number	Supersedes	Relays	Remarks
70-124-1	16-1351	16-722-2	788, 711, 388J (All)	Front Back (North South) Mount
70-124-2	16-1351	16-722-2	788, 711, 388J (All)	Front Back (North South) Mount
70-178-1	16-1351	16-722-2	788, 711, 388J (All)	Front Back (North South) Mount
70-178-2	16-1351	16-722-2	788, 711, 388J (All)	Front Back (North South) Mount
70-378-1	16-1342		782 (All & Hermetic)	Side Mount
70-378-1	16-1324		782C and Hermetic Only	Front Back (North South) Mount
70-378-1	16-TDR782SC		TDR782	Side Mount
70-379-1	16-1342		782 (All & Hermetic)	Side Mount
70-379-1	16-TDR782SC		TDR782	Side Mount
70-401-1	16-1342		782 With .187 Term.	Side Mount
70-401-1	16-1324		782C With .187 Term. Only	Front Back (North South) Mount
70-402-1	16-1342		782 With .187 Term.	Side Mount
70-402-1	16-1324		782C With .187 Term. Only	Front Back (North South) Mount
70-459-1	16-1342	16-1329	782 With .187 Term.	Side Mount
70-461-1	16-1342	16-1328	782 (All & Hermetic)	Side Mount
70-461-1	16-TDR782SC		TDR782	Side Mount
70-463-1	16-1351	16-1329	788 (All), 785	Side Mount
70-463-1	16-1344		TDR (SOX/SRX) B	Side Mount
70-464-1	16-1351	16-1352	750 (All), 750H	Side Mount
70-464-1	16-1344		TDRSOXP, 712	Side Mount
70-464-1	16-TDRPROSC		TDRPRO	Side Mount
70-465-1	16-1351	13-1352	750 (All), 750H, 755	Side Mount
70-465-1	16-1344		TDR (SRXP), 712	Side Mount
70-465-1	16-TDRPROSC		TDRPRO	Side Mount
70-750DL8-1	16-1332		750 (All)	Front Back (North South) Mount
70-750DL8-1	16-1344		TDRSOXP	Side Mount
70-750DL8-1	16-1351	16-1352	750H	Side Mount
70-750DL8-1	16-TDRPROSC		TDRPRO	Side Mount
70-750DL11-1	16-1332		750 (All)	Front Back (North South) Mount
70-750DL11-1	16-1344		TDRSRXP	Side Mount
70-750DL11-1	16-1351	16-1352	750H	Side Mount
70-750DL11-1	16-TDRPROSC		TDRPRO	Side Mount
70-750E8-1	16-1351	16-1352	750 (All), 750H	Side Mount
70-750E8-1	16-1344		750 (All), TDRSRXP, 712	Side Mount
70-750E8-1	16-TDRPROSC		TDRPRO	Side Mount
70-750E11-1	16-1351	16-1352	750 (All), 750H, 755	Side Mount
70-750E11-1	16-1344		TDRSRXP, 712	Side Mount
70-750E11-1	16-TDRPROSC		TDRPRO	Side Mount
70-750EL8-1	16-1351	16-1352	750 (All), 750H	Side Mount
70-750EL11-1	16-1351	16-1352	750 (All), 750H, 755	Side Mount
70-781D5-1A	16-781SC	16-1326	781 (All)	Side Mount
70-781D5-1A	16-781IDC	16-1327 (Plastic)	781 (All)	Side Mount
70-781F-1	16-781SC	16-1326	781 (All)	Side Mount
70-781T-1	16-781SC	16-1326	781 (All)	Side Mount
70-782D8-1	16-1342		782 With .187 Term.	Side Mount
70-782D8-1	16-782IDC	16-1349 (Plastic)	782 (All)	Side Mount
70-782D14-1	16-782SC		782, 4 Pole (Plain & Full Featured)	Side Mount
70-782D14-1	16-782PC		782, 4 Pole (Full Featured)	Side Mount
70-782D14-1	16-1342		782 Hermetic Only	Side Mount
70-782D14-1	16-TDR782SC		TDR782	Side Mount
70-782E14-1	16-782SC		782, 4 Pole (Plain & Full Featured)	Side Mount
70-782E14-1	16-782PC-1		782, 4 Pole (Full Featured)	Side Mount
70-782E14-1	16-1342		782 Hermetic Only	Side Mount
70-782E14-1	16-TDR782SC		TDR782	Side Mount
70-782EL8-1	16-782SC		782 2 Pole (All)	Side Mount
70-782EL8-1	16-782PC-1		782, 2 Pole (Full Featured)	Side Mount
70-782EL8-1	16-TDR782SC		TDR782	Side Mount
70-782EL11-1	16-782SC		782, 3 Pole (All)	Side Mount
70-782EL11-1	16-782PC-1		782, 3 Pole (Full Featured)	Side Mount
70-782EL14-1	16-782SC		782, 4 Pole (Plain & Full Featured)	Side Mount
70-782EL14-1	16-782PC-1		782, 4 Pole (Full Featured)	Side Mount
70-782EL14-1	16-1342		782 Hermetic Only	Side Mount
70-782EL14-1	16-TDR782SC		TDR782	Side Mount
70-783D11-1	16-783SC <i>COMING SOON!</i>		783 (All)	Side Mount
70-783D11-1	16-783IDC	16-1350 (Plastic)	783 (All)	Side Mount
70-784D14-1	16-784SC		784 (All)	Side Mount
70-784D14-1	16-784IDC	16-1351 (Plastic)	784 (All)	Side Mount
70-788EL11-1	16-1351		788 (All), 711	Side Mount