



2.5mm Phone Plug

17PP053-EX

KOBI CONN

2.5mm Phone Plug

17PP053-EX



Dimensions: In.

(except where noted)

SPECIFICATIONS	
Contact Resistance:	50mΩ max.
Insulation Resistance:	100MΩ min. @ 500VDC
Dielectric Strength:	500VAC for 1 Minute
Cap:	ABS Resin
Contact A:	Nickel Plated Brass
Contact B:	Nickel Plated Brass
Terminal A:	Nickel Plated Brass
Terminal B:	Nickel Plated Steel
Insulator A:	Ebonite
Insulator B:	Phenolic Resin
RoHS Compliant by Exemption	

Date Last Revised: 12-22-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300886

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[17PP053-EX](#)