

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080209](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Watertite Wet Location 26W Fluorescent Magnet Mount Machine Light, with 16/3 SJTOOW Cord Type, Overall Cord Length 4.57m (15.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374
UL E174254

General

Product Family Portable Lighting
Series [130108](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Wide-Area Lighting Products](#)
Product Name Watertite
Type Wide Area Lamps
UPC 78678806501

Physical


Cord Length - Primary 4.57m (15.0')
Cord Length - Secondary N/A
Depth 69.85mm (2.750")
Duty Industrial
Guard Included No
Guard Type N/A
Height N/A
Length 444.50mm (17.500")
Material - Globe Butyrate
Material - Guard Nitrile Rubber 80 Shore A
Mounting Style Magnetic-Bracket
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 16/3 SJTOOW
Lamp Type PL-C 26/41/4P
Lamp Wattage - Maximum 26W
Lumens 1800
On/Off Switch Yes
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 2126MS



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130108](#) Series