



313 2444 MINIATURLAMPEN / MINIATURE LAMPS

T - 10 x 28 (Ø 10 mm) Maßstab: 1:1 scale: 1:1					Socket / Base: BA 9s / E 10-13  0242  0246			
Spannung Voltage (V)	Stromstärke Current (mA) / (W)	Lichtausbeute Light output (M. S. C. P.)	Lebensdauer Lifetime (h) AC	Wendelaufbau Filament	EBT Nr. / Intern. Nr.			
4	100	0,14	5.000	C-2R	— / —	02461401	/	432
5	50	0,08	1.000	C-2R	02421600 / 438	—	/	—
5	90	0,25	750	C-2R	02421601 / 1850	02461601	/	439
6	75	0,32	100	C-6	02422201 / 1140	—	/	—
6	100	0,20	5.000	C-2R	02422405 / —	—	/	—
6	1,2 W	0,30	15.000	C-2R	02422601 / 1212	02462605	/	—
6	2 W	0,50	15.000	C-2R	02423000 / —	02462805	/	—
6,3	150	0,33	15.000	C-2R	02423401 / 755	—	/	—
6,3	150	0,52	3.000	C-2R	02423601 / 47	02463301	/	40
6,3	250	0,90	3.000	C-2R	02423901 / 44	02463801	/	46
6,5	300	0,96	4.000	C-2R	02425001 / 504	—	/	—
8	300	1,15	4.000	C-2R	02426001 / 528	—	/	—
10	138	0,88	300	C-2V	02426501 / 1280	—	/	—
12	1,2	0,25	10.000	C-2F	02426612 / 1221	—	/	—
12	100	0,40	5.000	C-2F	— / —	02466605	/	—
12	138	0,88	3.000	C-2V	02427101 / 643	02467001	/	1309
12	3 W	1,00	2.000	C-2V	02427200 / —	02467200	/	—
14	80	0,31	7.500	C-2F	02427501 / 756	—	/	—
14	200	1,40	3.000	C-2V	02427701 / 1815	—	/	—
14	330	2,00	3.000	C-2F	02428101 / 1893	—	/	—
24	1,2	0,25	10.000	C-2F	02428801 / 1210	—	/	—
24	50	0,32	5.000	C-2F	02428901 / 568	02468901	/	592
24	2 W	0,50	10.000	C-2F	02428903 / 1201	02469101	/	22
24/28	2 W	0,62	7.500	C-2F	02429101 / —	—	/	—
24	3 W	0,95	3.000	C-2F	02429301 / 600	02469301	/	599