



1085 HardBack Case



Interior dimensions:

36.3 x 26.3 x 5 cm (14" x 10" x 2")

Designed to protect 14" laptops

Watertight Gasket - Tight seal created when case is shut

The easy open latch remains shut under pressure or after impact

Automatic Purge Valve - Keeps water and dust out while balancing air pressure

Pick N Pluck™ with convoluted lid foam

Removable shoulder strap included

Legendary Guarantee of Excellence

Visit our

Watertight, crushproof, and dust proof



Black

1085 HardBack Case SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)			
39.7 x 31.5 x 6.3 cm (16" x 12" x 3")		36.3 x 26.3 x 5 cm (14" x 10" x 2")			
Lid Depth		Bottom Depth		Total Depth	
2.5 cm (1")		2.5 cm (0.99")		5 cm 1.97")	
Lid Depth		Bottom Depth		Total Depth	
2.5 cm (0.99")		2.5 cm (0.99")		5 cm 1.97")	
Weight w/Foam		Weight w/o Foam		Buoyancy Max.	
1.41 kg. (3.1 lbs)		1.2kg (2.65 lbs.)		0 kg (lbs.)	
Range Temperature					
-23 / 49° C (-10 / 120° F)					

Materials

Body	Latch	Lid O-Ring	Pins
ABS	ABS	EPDMStainless Steel	
Foam	Purge Body	Purge Vent	Purge O- Ring
	Polycarbonate	PTFE	70 Shore Nitrile

Configuration

Cat. #	Description
1085	1085 HardBack Case

1085 HardBack Case Accessories

No accessories are currently available for this product